

Rittal – The System.

Faster – better – everywhere.



SK 3210.500

Air-Water Heat Exchangers

State: 2026-05-14 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3210.500 - Air-Water Heat Exchangers roof-mounted

For mounting on the rooftop. Cooling output 1.87 – 4 kW. Protection category IP 55 as standard. Particularly suitable for use in harsh environments. Flexible water connection options.



Features

Model No.	SK 3210.500
Version	Water-carrying parts copper/brass (Cu/CuZn)
Product description	To be used in rough environments and temperature ranges of up to +70 °C. The air-to-water heat exchanger is installed on the roof of a control cabinet via flexible water connection options.
Color	RAL 7035
Supply includes	Wired ready for connection (plug-in terminal strip) Drilling template Sealing mat Fasteners
Total cooling output	L 35 W 10 at 400 l/h: 4 kW
Rated operating voltage	230 V, 1~, 50 Hz/60 Hz
Rated power Pel	At 50 Hz: 100 W At 60 Hz: 120 W
Rated current max.	At 50 Hz: 0.44 A At 60 Hz: 0.5 A
Permissible operating pressure (p. max.)	1: 10 bar

Features

Type of connection (electrical)	Plug-in terminal strip
Duty cycle	100 %
Cooling medium	Water (see Internet for specifications)
Water inlet temperature	1 °C...30 °C
Water connections	½" connector sleeve G ¾" external thread
Temperature control	e-Comfort Controller (factory setting +35 °C)
Operating temperature range	1 °C...70 °C
Dimensions	Width: 597 mm Height: 417 mm Depth: 475 mm
Protection category	IP 65 available on request
Pre-fuse	Miniature circuit-breaker/fuse: 4 A
Setting range	20 °C...55 °C
Protection category IP to EN 60529	IP 55
Packaging unit	1 pc(s).
Net weight	34.2 kg
Gross weight	36 kg
Customs tariff number	84158300
ETIM 9	EC002515
ETIM 8	EC002515
ECLASS 8.0	27180712
Product description	SK Air/water heat exchanger, roof-mounted, 13649 BTU/h 230 V, 1~, 50/60 Hz, comfort controller, water-carrying parts: copper/brass, WHD: 597 x 417 x 475 mm

Approvals

Approvals

CSA

UR + C-UR (recognized)

Explanations

Declaration of conformity