
Rittal – The System.

Faster – better – everywhere.





SK 3212.024 Air-Water Heat Exchangers

State: 2025-11-17 (Source: rittal.com/ca-en)



SK 3212.024 - Air-Water Heat Exchangers wall-mounted

Output categories 1023.64 - 17060.71 BTU/h. For use in tough environments. Convenient mounting options and flexible water connection options. External mounting or full internal mounting possible.

Features

Model No.	SK 3212.024	
Version	Water-carrying parts copper/brass (Cu/CuZn)	
Product description	To be used in rough environments and temperature ranges of up to +70 °C. Convenient assembly options and flexible water connection options. Partial or full internal mounting possible.	
Color	RAL 7035	
Supply includes	Wired ready for connection Drilling template Sealing and assembly components	
Total cooling output	L 35 W 10 at 200 l/h: 0.3 kW	
Rated operating voltage	24 V (DC)	
Rated current max.	with DC: 1.2 A	
Permissible operating pressure (p. max.)	1 - 10 bar	
Duty cycle	100 %	
Cooling medium	Water (see Internet for specifications)	
Water inlet temperature	1 °C30 °C	
Water connections	%" connector sleeve	
Operating temperature range	1 °C70 °C	
Note	Integral non-return valve for version with e-Comfort controller	
Dimensions	Width: 150 mm Height: 300 mm Depth: 85 mm	

© Rittal 2025 2

Features

Pre-fuse	Miniature circuit-breaker/fuse: 4 A
Setting range	20 °C55 °C
Protection category IP to EN 60 529	IP 55
Packaging unit	1 pc(s).
Net weight	3.038
Gross weight	3.238
Customs tariff number	84158300
EAN	4028177430921
ETIM 9	EC002515
ETIM 8	EC002515
ECLASS 8.0	27180712

Approvals

eclaration of conformity

© Rittal 2025 3