

# Rittal – The System.

Faster – better – everywhere.



## SK 3214.700

## Air-Water Heat Exchangers

State: 2025-09-13 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3214.700 - Air-Water Heat Exchangers Wall-mounted HD

Air/water heat exchanger for production areas in the food and beverage industry where hygiene is important – the perfect addition to the Rittal Hygienic Design range. The easy-to-clean design reduces the risk of contamination and ensures food safety.



## Features

Model No.	SK 3214.700
Version	Water-carrying parts copper/brass (Cu/CuZn)
Product description	Air/water heat exchanger for production areas in the food sector with high hygienic requirements – the ideal supplement to the Rittal Hygienic Design Program. Its easy-clean design reduces the risk of contamination and guarantees food safety.
Benefits	Easy-clean and hygiene-compliant design A roof slope of 30° prevents objects from being placed on them and allows liquid to run off quickly An all-round external, replaceable silicone seal prevents the build-up of dirt between the enclosure and the air-water heat exchanger.
Material	Housing: Stainless steel 1.4301 (AISI 304)
Surface finish	Housing: Brushed, grain 400, peak-to-valley height < 0.8 µm
Supply includes	Wired ready for connection Drilling template Sealing and assembly components

# Features

Total cooling output	L 35 W 10 at 200 l/h: 0.6 kW L 35 W 10 at 400 l/h: 0.65 kW
Rated operating voltage	230 V, 1~, 50 Hz/60 Hz
Rated power Pel	At 50 Hz: 33 W At 60 Hz: 34 W
Rated current max.	At 50 Hz: 0.16 A At 60 Hz: 0.14 A
Permissible operating pressure (p. max.)	1 - 10 bar
Duty cycle	100 %
Cooling medium	Water (see Internet for specifications)
Water inlet temperature	1 °C...30 °C
Water connections	G 3/8" external thread
Temperature control	Thermostat-controlled solenoid valve
Temperature monitoring	Internal thermostat, with change-over contact, switching load 16 A, setting range +20 °C ... +60 °C (factory setting +35 °C)
Operating temperature range	1 °C...70 °C
Note	In order to achieve protection category IP 66/69 as per IEC 60 529, the ingress of leakage air through the condensation drain openings must be completely prevented.
Dimensions	Width: 220 mm Height: 526 mm Depth: 100 mm
Pre-fuse	Miniature circuit-breaker/fuse: 2 A
Setting range	20 °C...60 °C
Protection category IP to EN 60 529	IP 56/59
Protection category NEMA	NEMA 4X
Packaging unit	1 pc(s).
Net weight	6

# Features

Gross weight	6.86
Customs tariff number	84158300
EAN	4028177806399
ETIM 9	EC002515
ETIM 8	EC002515
ECLASS 8.0	27180712

# Approvals

Approvals	CSA UL + C-UL - FTTA UR + C-UR (recognized)
Explanations	Declaration of conformity