Rittal – The System.

Faster – better – everywhere.






SK 3216.480 Air-Water Heat Exchangers

State: 2025-12-03 (Source: rittal.com/ca-en)



SK 3216.480 - Air-Water Heat Exchangers wall-mounted

Output class 23,885 BTU/hr. For use in tough environments. With thermostat-controlled solenoid valve.



Features

Model No.	SK 3216.480
Version	Water-carrying parts copper/brass (Cu/CuZn)
Product description	To be used in rough environments and temperature ranges of up to +70°C. With thermostat-controlled solenoid valve.
Material	Copper/brass (Cu/CuZn)
Color	RAL 7035
Supply includes	Wired ready for connection (plug-in terminal strip) Sealing and assembly components
Total cooling output	L 35 W 10 at 500 l/h: 7 kW
Rated operating voltage	400 V, 3~, 50 Hz 480 V, 3~, 60 Hz
Rated current max.	At 50 Hz: 1.4 A At 60 Hz: 1.2 A
Permissible operating pressure (p. max.)	1 - 10 bar
Duty cycle	100 %
Cooling medium	Water (see Internet for specifications)

© Rittal 2025

Features

Water inlet temperature	1 °C30 °C
Water connections	½" connector sleeve G ¾" external thread
Temperature control	Thermostat-controlled solenoid valve
Temperature monitoring	Internal thermostat, with change-over contact, switching load 16 A, setting range +20 °C +60 °C (factory setting +35 °C)
Operating temperature range	1 °C70 °C
Note	Use 3-pole miniature circuit-breaker
Dimensions	Width: 450 mm Height: 1,800 mm Depth: 300 mm
Note on Model No.:	Delivery times on request.
Pre-fuse	Miniature circuit-breaker/fuse: 4 A
Pre-fuse	Motor circuit-breaker: 1.42 A
Setting range	20 °C55 °C
Protection category IP to EN 60 529	IP 55
Packaging unit	1 pc(s).
Net weight	80
Gross weight	90
Customs tariff number	84158300
EAN	4028177458642
ETIM 9	EC002515
ETIM 8	EC002515
ECLASS 8.0	27180712

Approvals

© Rittal 2025 3

Approvals

Explanations

Declaration of conformity

© Rittal 2025