


# Rittal – The System.

Faster – better – everywhere.



## SK 3237.055

# Chopped fiber filter mat

State: 2026-06-28 (Source: [rittal.com/ca-en](https://rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3237.055 - Chopped fiber filter mat

Replacement filter mats for roof fans, filter fans or thermoelectric coolers to effectively protect control enclosure components from dirt, dust and water.

## Features

|                        |   |
|------------------------|---|
| Model No.              | SK 3237.055   |
| Version                | for filter fans   |
| Product description    | Made of chopped-fiber mat with a progressive construction. Temperature-resistant to 100 °C, self-extinguishing category F1 to DIN 53 438. Dust-laden air side: Open structure. Clean air side: Closed structure. Reliable filtering of virtually all types of dust from a particle size of 10 µm. |
| Material               | Chemical fibers   |
| Color                  | White   |
| Note                   | Not suitable for use in EMC filter fans.  |
| Suitable for Model No. | 3237.3xx/3237.7xx   |
| Dimensions             | Width: 89 mm<br>Height: 89 mm<br>Depth: 10 mm   |
| Filter class           | to DIN EN 779: G2<br>to DIN EN ISO 16890: ISO coarse 50%  |
| Packaging unit         | 50 pc(s).   |
| Net weight             | 0.05 kg   |
| Gross weight           | 0.164 kg  |
| Customs tariff number  | 56039390  |
| ETIM 9                 | EC002513  |
| ETIM 8                 | EC002513  |
| ECLASS 8.0             | 27180706  |

# Features

---

|                     |   |
|---------------------|---|
| Product description | SK chopped-fiber filter mat, for filter fan SK 3237.7xx/3237.3xx,<br>WHD: 89 x 89 x 10 mm |
|---------------------|---|

# Approvals

---

|           |                               |
|-----------|-------------------------------|
| Approvals | CSA<br>UR + C-UR (recognized) |
|-----------|-------------------------------|