## Rittal – The System.

Faster - better - everywhere.





# SK 3237.810 Blue e+ filter fan

State: 2025-10-27 (Source: rittal.com/ca-en)



#### SK 3237.810 - Blue e+ filter fan EMC

Complete fan unit with EMC shielding for tool-free mounting on surfaces. Air throughput from  $20-900 \; \text{m}^3\text{/h}$ 







#### **Features**

Model No.	SK 3237.810
Version	wall-mounted EMC
Product description	EMC fan-and-filter units have a high screening/dampening effect and meet performance level 2 as per EN 61587-3.
Benefits	Easy filter change thanks to a new opening mechanism on the louvre grille Faster assembly on the enclosure due to optimized snap hooks Diagonal fan technology ensures more uniform and consistent ventilation of the control cabinet through higher pressure stability Tool-free mounting
Material	Plastic
Color	RAL 7035
Supply includes	Complete unit ready to install, including EMC filter mat
Fan	Axial, shaded pole motor
Unimpeded air flow (with chopped fiber filter)	At 50 Hz: 20 m³/h At 60 Hz: 25 m³/h

© Rittal 2025 2

#### **Features**

Airflow with corresponding outlet filter including chopped fiber filter	At 50 Hz: 15 m³/h At 60 Hz: 18 m³/h
Rated operating voltage	115 V, 1~, 50 Hz/60 Hz
Rated power Pel	At 50 Hz: 12 W At 60 Hz: 10 W
Rated current max.	At 50 Hz: 0.14 A At 60 Hz: 0.13 A
Dimensions	Width: 116.5 mm Height: 116.5 mm Depth: 64.5 mm
Installation depth	46 mm
Mounting cut-out	Width of opening: 92 mm Cut-out height: 92 mm
Protection category IP to IEC 60 529	IP 54 with fleece filter IP 56 with fleece filter and hose-proof hood
Protection category NEMA	Type 12 with fleece filter Type 3, 3R with fleece filter and hose-proof hood
Pre-fuse	Miniature circuit-breaker/fuse: 2 A
Note	To improve energy efficiency and increase equipment service life, we recommend thermostats or temperature displays.
Operating temperature range	-15 °C55 °C
Storage temperature range	-30 °C70 °C
Noise pressure level	At 50 Hz: 42 dB(A) At 60 Hz: 47 dB(A)
Packaging unit	1 pc(s).
Net weight	0.4
Customs tariff number	84145915
EAN	4028177998254
ETIM 9	EC000320
ETIM 8	EC000320

© Rittal 2025 3

### Features

ECLASS 8.0 27180716

## **Approvals**

Approvals	CSA
	30 - KC Korea
	UL + C-UL - FTTA
	UR + C-UR (recognized)
Explanations	Declaration of conformity

© Rittal 2025 4