

Rittal – The System.

Faster – better – everywhere.



SK 3238.300 Blue e+ outlet filter

State: 2025-05-06 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3238.300 - Blue e+ outlet filter

For ventilation by convection, an outlet filter can be installed in the upper and lower sections of the enclosure.



Features

Model No.	SK 3238.300
Version	wall-mounted
Benefits	Easy filter change thanks to a new opening mechanism on the louvre grille Faster assembly on the enclosure due to optimized snap hooks Tool-free mounting
Material	Plastic
Color	RAL 7035
Supply includes	Outlet Filters Pleated filter
Mounting cut-out	Width of opening: 124 mm Cut-out height: 124 mm
Note	The outlet filter is UL Type 1 with the supplied pleated filter. To achieve UL Type 12 replace included filter with a fleece filter, purchased separately.
Suitable for Model No.	SK 3238.7xx

Features

Dimensions	Width: 148.5 mm Height: 148.5 mm Depth: 34.2 mm
Protection category NEMA	Type 1 with folded filter Type 12 with fleece filter Type 3, 3R, 4, 4X with fleece filter/folded filter and hose-proof hood
Protection category IP to IEC 60 529	IP 54 with fleece filter/folded filter IP 55 with folded filter and absorber mat IP56 with fleece filter/folded filter and hose-proof hood
Packaging unit	1 pc(s).
Net weight	0.161
Gross weight	0.206
Customs tariff number	39269097
EAN	4028177997653
ETIM 9	EC002513
ETIM 8	EC002513
ECLASS 8.0	27180706

Approvals

Approvals	UL + C-UL - FTTA UR + C-UR (recognized)
-----------	--