Rittal – The System.

Faster – better – everywhere.





SK 3201.300 Thermoelectric Cooler

State: 2025-11-18 (Source: rittal.com/ca-en)



SK 3201.300 - Thermoelectric Cooler Cooling/heating output 273/273 BTU/h

The powerful, lightweight climate control units based on Peltier technology provide efficient cooling of command panels and small enclosures. Cooling/heating output 273/273 BTU/h.

Features

Model No.	SK 3201.300
Product description	The powerful thermoelectric cooling unit in a lightweight design for the climate control of command panels and small enclosures.
Material	Device: Aluminum, anodized
General color	RAL 7015
Color	Cover: RAL 7015
Supply includes	Thermoelectric climate control unit Wired ready for connection (plug-in terminal strip) Mounting Accessories Filter Mat USB cable A/B Drilling template
Total cooling output to DIN EN 14511	Cooling output L35 L35/50 Hz: 80 W
Total cooling output L35 L30	Cooling output L35 L30/50 Hz : 100 W
Rated operating voltage	24 V (DC)
Rated current max.	4.5 A
Start-up current	4.5 A
Air throughput (unimpeded air flow)	External circuit: 45 m³/h Internal circuit: 45 m³/h
Energy efficiency ratio (EER) 50/60 Hz L35 L35	Refrigeration factor L35 L35 (EER) 50 Hz: 0.9
Thermal output	80 W
Version	wall-mounted

© Rittal 2025

2

Features

Dimensions	Width: 125 mm
	Height: 400 mm
	Depth: 155 mm
Protection category IP to EN 60	External circuit, IP 34
529	Internal circuit, IP 54
Type of connection (electrical)	Plug-in Spring Connection Terminal
Temperature control	PID control (factory setting: cooling +35 °C / heating +5 °C)
Operating temperature range	-30 °C55 °C
Setting range – cooling	5 °C55 °C
Setting range – heating	-10 °C20 °C
Pre-fuse	Miniature circuit-breaker/fuse: 10 A
Packaging unit	1 pc(s).
Net weight	3.249
Gross weight	3.449
Customs tariff number	84186900
EAN	4028177598621
E-Number Sweden	E3404552
ETIM 9	EC000855
ETIM 8	EC000855
ECLASS 8.0	27180704

Approvals

Certificates	EAC
Explanations	Declaration of conformity Declaration of conformity - F-gas regulation
	Declaration of conformity UK

© Rittal 2025 3