Rittal – The System.

Faster – better – everywhere.





SK 3237.724 Blue e+ filter fan


State: 2025-12-01 (Source: rittal.com/ca-en)



SK 3237.724 - Blue e+ filter fan

Complete fan unit for tool-free mounting on surfaces. Air throughput from 11 - 682.75 cfm, protection category IP 54 as standard.







Features

Model No.	SK 3237.724
Version	wall-mounted
Product description	Filter fans with diagonal fan technology are more pressure-resistant and produce more constant air performance. The diagonal outflow direction ensures a more uniform heat dissipation from the enclosure.
Benefits	Easy filter change thanks to a new opening mechanism on the louvre grille Faster assembly on the enclosure due to optimized snap hooks Diagonal fan technology ensures more uniform and consistent ventilation of the control cabinet through higher pressure stability. Tool-free mounting
Material	Plastic
Color	RAL 7035
Supply includes	Complete unit ready to install, including chopped fiber filter mat
Fan	Axial, DC motor
Unimpeded air flow (with chopped fiber filter)	with DC: 20 m³/h

© Rittal 2025

Features

with DC: 15 m³/h
24 V (DC)
with DC: 1.4 W
with DC: 0.06 A
Width: 116.5 mm Height: 116.5 mm Depth: 64.5 mm
46 mm
Width of opening: 92 mm Cut-out height: 92 mm
IP 54 with fleece filter IP 56 with fleece filter and hose-proof hood
Type 12 with fleece filter Type 3, 3R with fleece filter and hose-proof hood
Miniature circuit-breaker/fuse: 2 A
For the 3237.XXX filter fan, the electrical connection is made via 2 individual wires (length approx. 300 mm) on the unit, for all other filter fans, it's made via a spring-loaded terminal
-15 °C55 °C
-30 °C70 °C
with DC: 42 dB(A)
1 pc(s).
0.21
0.292
84145915
4028177998278
EC000320
EC000320
27180716

© Rittal 2025 3

Approvals

Approvals	30 - KC Korea
	UL + C-UL - FTTA
	UR + C-UR (recognized)
Explanations	Declaration of conformity

© Rittal 2025