Rittal – The System.

Faster - better - everywhere.





SK 3238.700 Blue e+ filter fan

State: 2025-11-23 (Source: rittal.com/ca-en)



SK 3238.700 - Blue e+ filter fan

Complete fan unit for tool-free mounting on surfaces. Air throughput from 11 - 682.75 cfm, protection category IP 54 as standard.







Features

Model No.	SK 3238.700
Version	wall-mounted
Product description	Filter fans with diagonal fan technology are more pressure-resistant and produce more constant air performance. The diagonal outflow direction ensures a more uniform heat dissipation from the enclosure.
Benefits	Highest airflow through pleated filter in delivery condition Easy filter change thanks to a new opening mechanism on the louvre grille Faster assembly on the enclosure due to optimized snap hooks Diagonal fan technology ensures more uniform and consistent ventilation of the control cabinet through higher pressure stability. Tool-free mounting
Material	Plastic
Color	RAL 7035
Supply includes	Complete unit ready to install, including pleated filter
Fan	Axial, shaded pole motor
Unimpeded air flow (with chopped fiber filter)	At 50 Hz: 53 m³/h At 60 Hz: 64 m³/h

© Rittal 2025

Features

Unimpeded air flow (with pleated	At 50 Hz: 63 m³/h
filter)	At 60 Hz: 72 m³/h
Airflow with corresponding outlet	At 50 Hz: 40 m³/h
filter including chopped fiber filter	At 60 Hz: 46 m³/h
Airflow with corresponding outlet	At 50 Hz: 49 m³/h
filter including pleated filter	At 60 Hz: 55 m³/h
Rated operating voltage	230 V, 1~, 50 Hz/60 Hz
Rated power Pel	At 50 Hz: 14.7 W
	At 60 Hz: 16.5 W
Rated current max.	At 50 Hz: 0.1 A
	At 60 Hz: 0.12 A
Dimensions	Width: 148.5 mm
	Height: 148.5 mm
	Depth: 82.5 mm
Installation depth	64 mm
Mounting cut-out	Width of opening: 124 mm
	Cut-out height: 124 mm
Protection category IP to IEC 60	IP 54 with chopped fiber filter/pleated filter
529	IP 55 with pleated filter and absorber mat
	IP 56 with chopped fiber filter/pleated filter and hose-proof hood
Protection category NEMA	Type 12 with chopped fiber filter/pleated filter
	Type 3, 3R, 4, 4X with chopped fiber filter/pleated filter and hose- proof hood
Pre-fuse	Miniature circuit-breaker/fuse: 2 A
Note	For the 3237.XXX filter fan, the electrical connection is made via 2
	individual wires (length approx. 300 mm) on the unit, for all other
	filter fans, it's made via a spring-loaded terminal
Operating temperature range	-15 °C55 °C
Storage temperature range	-30 °C70 °C
Noise pressure level	At 50 Hz: 52 dB(A)
	At 60 Hz: 54 dB(A)
Packaging unit	1 pc(s).

© Rittal 2025 3

Features

Net weight	0.66
Gross weight	0.86
Customs tariff number	84145915
EAN	4028177997615
ETIM 9	EC000320
ETIM 8	EC000320
ECLASS 8.0	27180716

Approvals

Approvals	CSA
	30 - KC Korea
	UL + C-UL - FTTA
	UR + C-UR (recognized)
Explanations	Declaration of conformity

© Rittal 2025