

# Rittal – The System.

Faster – better – everywhere.



## SK 3240.810 Blue e+ filter fan

State: 2026-04-11 (Source: [rittal.com/ca-en](http://rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3240.810 - Blue e+ filter fan EMC

Complete fan unit with EMC shielding for tool-free mounting on surfaces. Air throughput from 20–900 m<sup>3</sup>/h



## Features

|  |  |
|--|--|
| Model No.                                      | SK 3240.810  |
| Version  | wall-mounted<br>EMC  |
| Product description                            | EMC fan-and-filter units have a high screening/dampening effect and meet performance level 2 as per EN 61587-3.  |
| Benefits                                       | Easy filter change thanks to a new opening mechanism on the louvre grille<br>Faster assembly on the enclosure due to optimized snap hooks<br>Diagonal fan technology ensures more uniform and consistent ventilation of the control cabinet through higher pressure stability.<br>Tool-free mounting |
| Material                                       | Plastic  |
| Color  | RAL 7035   |
| Supply includes                                | Complete unit ready to install, including EMC filter mat   |
| Fan  | Diagonal, shaded pole motor  |
| Unimpeded air flow (with chopped fiber filter) | At 50 Hz: 175 m <sup>3</sup> /h<br>At 60 Hz: 157 m <sup>3</sup> /h   |

# Features

|   |   |
|---|---|
| Airflow with corresponding outlet filter including chopped fiber filter | At 50 Hz: 130 m <sup>3</sup> /h<br>At 60 Hz: 112 m <sup>3</sup> /h  |
| Rated operating voltage   | 115 V, 1~, 50 Hz/60 Hz  |
| Rated power Pel   | At 50 Hz: 35.5 W<br>At 60 Hz: 38.2 W  |
| Rated current max.  | At 50 Hz: 0.41 A<br>At 60 Hz: 0.42 A  |
| Dimensions  | Width: 255 mm<br>Height: 255 mm<br>Depth: 129 mm  |
| Installation depth  | 108 mm  |
| Mounting cut-out  | Width of opening: 224 mm<br>Cut-out height: 224 mm  |
| Protection category IP to IEC 60 529                                    | IP 54 with fleece filter<br>IP 56 with fleece filter and hose-proof hood  |
| Protection category NEMA  | Type 12 with fleece filter<br>Type 3, 3R, 4, 4X with fleece filter and hose-proof hood                              |
| Pre-fuse  | Miniature circuit-breaker/fuse: 4 A   |
| Note  | To improve energy efficiency and increase equipment service life, we recommend thermostats or temperature displays. |
| Operating temperature range   | -30 °C...55 °C  |
| Storage temperature range   | -30 °C...70 °C  |
| Noise pressure level  | At 50 Hz: 48 dB(A)<br>At 60 Hz: 45 dB(A)  |
| Packaging unit  | 1 pc(s).  |
| Net weight  | 1.82 kg   |
| Gross weight  | 1.82 kg   |
| Customs tariff number   | 84145915  |
| ETIM 9  | EC000320  |
| ETIM 8  | EC000320  |

# Features

---

|            |          |
|------------|----------|
| ECLASS 8.0 | 27180716 |
|------------|----------|

---

|                     |   |
|---------------------|---|
| Product description | SK Blue e+ filter fan, EMC, 175/157 m <sup>3</sup> /h, 115 V, 1~, 50 Hz/60 Hz, WHD 255 x 255 x 129 mm, RAL 7035 |
|---------------------|---|

# Approvals

---

|           |  |
|-----------|--|
| Approvals | CSA<br>30 - KC Korea<br>UL + C-UL - FTFA<br>UR + C-UR (recognized) |
|-----------|--|

---

|              |                           |
|--------------|---------------------------|
| Explanations | Declaration of conformity |
|--------------|---------------------------|