

Rittal – The System.

Faster – better – everywhere.



SK 3239.500

TopTherm Filter Fan Units

State: 2026-05-22 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3239.500 - TopTherm Filter Fan Units with EC technology

Energy-efficient design of the RTT filter fans with EC technology. From 105.94 cfm with integrated control interface (0-10 V / PWM input and tachometer output signal) for controlling and monitoring the fan.

Features

| | |
|--|---|
| Model No. | SK 3239.500 |
| Version | wall-mounted EC |
| Product description | Energy-efficient version of the TopTherm filter fans with diagonal fan technology. Fan 3240.50x to 3245.51x may be controlled and monitored. The fan may be activated via the control interface with tacho signal output integrated as standard. Also, monitoring of the fan speed and function is supported. |
| Product changes | Since May 2024, the cover for the connection terminal is no longer part of the TopTherm filter fan. During testing, it was found not to be required by the standards and does not impair function or operational safety. |
| Color | RAL 7035 |
| Supply includes | Complete unit ready to install, including chopped fiber filter mat |
| Fan | Diagonal, EC motor |
| Unimpeded air flow (with pleated filter) | At 50 Hz: 110 m ³ /h At 60 Hz: 125 m ³ /h |
| Unimpeded air flow (with chopped fiber filter) | At 50 Hz: 100 m ³ /h At 60 Hz: 100 m ³ /h |
| Air throughput with outlet filter incl. chopped fiber filter mat (quantity x order number) | 1 x 3239200: 74 m ³ /h 2 x 3239200: 84 m ³ /h |
| Rated operating voltage | 200 V - 240 V, 1~, 50 Hz/60 Hz |

Features

| | |
|--------------------------------------|--|
| Rated power Pel | At 50 Hz: 5.8 W At 60 Hz: 5.8 W |
| Rated current max. | At 50 Hz: 0.045 A At 60 Hz: 0.045 A |
| Dimensions | Width: 204 mm Height: 204 mm |
| Installation depth | 90 mm |
| Mounting cut-out | Width of opening: 177 mm Cut-out height: 177 mm |
| Protection category IP to IEC 60 529 | IP 54 with chopped fiber filter/pleated filter IP 55 with pleated filter and absorber mat IP 56 with chopped fiber filter/pleated filter and hose-proof hood |
| Protection category NEMA | Type 12 with chopped fiber filter/pleated filter Type 3 Type 3R Type 4 Type 4X with chopped fiber filter/pleated filter and hose-proof hood |
| Pre-fuse | Miniature circuit-breaker/fuse: 6 A |
| Note | A pleated filter can optionally be used to increase the air throughput (see characteristic curve). This can be used with both the filter & roof-mounted fans and the exhaust filters. For even more efficient operation or for monitoring the fan-and-filter units, we recommend the use of a speed control EC for EC fan-and-filter unit (from air flow rates of 180 m ³ /h). |
| Operating temperature range | -20 °C...55 °C |
| Storage temperature range | -30 °C...70 °C |
| Noise pressure level | At 50 Hz: 53 dB(A) At 60 Hz: 53 dB(A) |
| Packaging unit | 1 pc(s). |
| Net weight | 0.8 kg |
| Gross weight | 0.91 kg |
| Customs tariff number | 84145915 |

Features

| | |
|---------------------|--|
| ETIM 9 | EC000320 |
| ETIM 8 | EC000320 |
| ECLASS 8.0 | 27180716 |
| Product description | SK Fan-and-filter unit TopTherm, 58.9 cfm 200-240 V, 1~, 50/60 Hz, WHD: 204 x 204 x 24 mm, EC technology |

Approvals

| | |
|--------------|---|
| Approvals | CSA UL + C-UL - FTTA UR + C-UR (recognized) |
| Explanations | Declaration of conformity Declaration of conformity UK |