Rittal – The System.

Faster – better – everywhere.





SK 3243.500 TopTherm Filter Fan Units

State: 2025-11-04 (Source: rittal.com/ca-en)



SK 3243.500 - TopTherm Filter Fan Units with EC technology

Energy-efficient design of the RTT filter fans with EC technology. From 105.94 cfm with integrated control interface (0-10 V / PWM input and tachometer output signal) for controlling and monitoring the fan.

Features

Model No.	SK 3243.500
Version	wall-mounted EC
Product description	Energy-efficient version of the TopTherm filter fans with diagonal fan technology. Fan 3240.50x to 3245.51x may be controlled and monitored. The fan may be activated via the control interface with tacho signal output integrated as standard. Also, monitoring of the fan speed and function is supported.
Product modification	Since May 2024, the cover for the connection terminal is no longer part of the TopTherm filter fan. During testing, it was found not to be required by the standards and does not impair function or operational safety. Le recouvrement pour la borne de raccordement ne fait plus partie des ventilateurs à filtre TopTherm depuis mai 2024. Lors de la vérification, il s'est avéré qu'elle n'est pas nécessaire d'un point de vue normatif et qu'elle ne constitue pas une altération de la fonction ni de la sécurité de fonctionnement.
Color	RAL 7035
Supply includes	Complete unit ready to install, including chopped fiber filter mat
Fan	Diagonal, EC motor
Unimpeded air flow (with chopped fiber filter)	At 50 Hz: 540 m³/h At 60 Hz: 540 m³/h
Unimpeded air flow (with pleated filter)	At 50 Hz: 625 m³/h At 60 Hz: 716 m³/h

© Rittal 2025 2

Features

Air throughput with outlet filter	
incl. chopped fiber filter mat (quantity x order number)	1 x 3243200: 405 m³/h 2 x 3243200: 475 m³/h
Rated operating voltage	200 V - 240 V, 1~, 50 Hz/60 Hz
Rated power Pel	At 50 Hz: 51 W At 60 Hz: 51 W
Rated current max.	At 50 Hz: 0.5 A At 60 Hz: 0.5 A
Dimensions	Width: 323 mm Height: 323 mm
Installation depth	118.5 mm
Mounting cut-out	Width of opening: 292 mm Cut-out height: 292 mm
Protection category IP to IEC 60 529	IP 54 with chopped fiber filter/pleated filter IP 55 with pleated filter and absorber mat IP 56 with chopped fiber filter/pleated filter and hose-proof hood
Protection category NEMA	Type 12 with chopped fiber filter/pleated filter Type 3
	Type 3R Type 4 Type 4X with chopped fiber filter/pleated filter and hose-proof hood
Control interface	Type 4
Control interface Pre-fuse	Type 4 Type 4X with chopped fiber filter/pleated filter and hose-proof hood
	Type 4 Type 4X with chopped fiber filter/pleated filter and hose-proof hood Yes
Pre-fuse	Type 4X with chopped fiber filter/pleated filter and hose-proof hood Yes Miniature circuit-breaker/fuse: 6 A A pleated filter can optionally be used to increase the air throughput (see characteristic curve). This can be used with both the filter & roof-mounted fans and the exhaust filters. For even more efficient operation or for monitoring the fan-and-filter units, we recommend the use of a speed control EC for EC fan-and-
Pre-fuse Note	Type 4X with chopped fiber filter/pleated filter and hose-proof hood Yes Miniature circuit-breaker/fuse: 6 A A pleated filter can optionally be used to increase the air throughput (see characteristic curve). This can be used with both the filter & roof-mounted fans and the exhaust filters. For even more efficient operation or for monitoring the fan-and-filter units, we recommend the use of a speed control EC for EC fan-and-filter unit (from air flow rates of 180 m³/h).

© Rittal 2025 3

Features

Packaging unit	1 pc(s).
Net weight	2.72
Gross weight	3.38
Customs tariff number	84145915
EAN	4028177652156
ETIM 9	EC000320
ETIM 8	EC000320
ECLASS 8.0	27180716

Approvals

Approvals	CSA UL + C-UL - FTTA UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity UK

© Rittal 2025