

# Rittal – The System.

Faster – better – everywhere.



## SK 3243.718 Blue e+ filter fan

State: 2026-07-10 (Source: [rittal.com/ca-en](http://rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3243.718 - Blue e+ filter fan

Complete fan unit for tool-free mounting on surfaces. Air throughput from 11 - 682.75 cfm, protection category IP 54 as standard.



## Features

|  |  |
|--|--|
| Model No.                                | SK 3243.718  |
| Version                                  | wall-mounted   |
| Product description                      | Filter fans with diagonal fan technology are more pressure-resistant and produce more constant air performance. The diagonal outflow direction ensures a more uniform heat dissipation from the enclosure.   |
| Benefits                                 | Highest airflow through pleated filter in delivery condition<br>Easy filter change thanks to a new opening mechanism on the louvre grille<br>Faster assembly on the enclosure due to optimized snap hooks<br>Diagonal fan technology ensures more uniform and consistent ventilation of the control cabinet through higher pressure stability.<br>Tool-free mounting |
| Material                                 | Plastic  |
| Color                                    | RAL 9005   |
| Supply includes                          | Complete unit ready to install, including pleated filter   |
| Fan                                      | Diagonal, 1~ capacitor motor   |
| Unimpeded air flow (with pleated filter) | At 50 Hz: 625 m <sup>3</sup> /h<br>At 60 Hz: 716 m <sup>3</sup> /h   |

# Features

|   |  |
|---|--|
| Airflow with corresponding outlet filter including pleated filter       | At 50 Hz: 565 m <sup>3</sup> /h<br>At 60 Hz: 645 m <sup>3</sup> /h   |
| Unimpeded air flow (with chopped fiber filter)                          | At 50 Hz: 540 m <sup>3</sup> /h<br>At 60 Hz: 590 m <sup>3</sup> /h   |
| Airflow with corresponding outlet filter including chopped fiber filter | At 50 Hz: 444 m <sup>3</sup> /h<br>At 60 Hz: 498 m <sup>3</sup> /h   |
| Rated operating voltage   | 115 V, 1~, 50 Hz/60 Hz   |
| Rated power Pel   | At 50 Hz: 78.7 W<br>At 60 Hz: 102.8 W  |
| Rated current max.  | At 50 Hz: 0.81 A<br>At 60 Hz: 0.9 A  |
| Dimensions  | Width: 323 mm<br>Height: 323 mm<br>Depth: 144.5 mm   |
| Installation depth  | 124 mm   |
| Mounting cut-out  | Width of opening: 292 mm<br>Cut-out height: 292 mm   |
| Protection category IP to IEC 60 529                                    | IP 54 with chopped fiber filter/pleated filter<br>IP 55 with pleated filter and absorber mat<br>IP 56 with chopped fiber filter/pleated filter and hose-proof hood                           |
| Protection category NEMA  | Type 12 with chopped fiber filter/pleated filter<br>Type 3, 3R, 4, 4X with chopped fiber filter/pleated filter and hose-proof hood   |
| Pre-fuse  | Miniature circuit-breaker/fuse: 6 A  |
| Note  | For the 3237.XXX filter fan, the electrical connection is made via 2 individual wires (length approx. 300 mm) on the unit, for all other filter fans, it's made via a spring-loaded terminal |
| Operating temperature range   | -30 °C...55 °C   |
| Storage temperature range   | -30 °C...70 °C   |
| Noise pressure level  | At 50 Hz: 62 dB(A)<br>At 60 Hz: 65 dB(A)   |
| Packaging unit  | 1 pc(s).   |

# Features

---

|                       |   |
|-----------------------|---|
| Net weight            | 3.12 kg   |
| Gross weight          | 3.12 kg   |
| Customs tariff number | 84145915  |
| ETIM 9                | EC000320  |
| ETIM 8                | EC000320  |
| ECLASS 8.0            | 27180716  |
| Product description   | SK Blue e+ filter fan, 625/716 m <sup>3</sup> /h, 115 V, 1~, 50 Hz/60 Hz, WHD<br>323 x 323 x 144.5 mm, RAL 9005 |

# Approvals

---

|              |  |
|--------------|--|
| Approvals    | CSA<br>30 - KC Korea<br>UL + C-UL - FTTA<br>UR + C-UR (recognized) |
| Explanations | Declaration of conformity  |