

# Rittal – The System.

Faster – better – everywhere.



## SK 3245.910 Blue e+ filter fan

State: 2026-05-04 (Source: [rittal.com/ca-en](http://rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3245.910 - Blue e+ filter fan with EC technology

The energy-efficient design with EC technology is characterized not only by its first-time IoT capability. The Blue e+ filter fan also opens the door to many other advantages – from energy efficiency to monitoring and sustainability to higher air performance (175 - 1,160 m<sup>3</sup>/h).



## Features

Model No.	SK 3245.910
Version	wall-mounted EC
Benefits	Highest airflow through pleated filter in delivery condition Easy filter change thanks to a new opening mechanism on the louvre grille Faster assembly on the enclosure due to optimized snap hooks Diagonal fan technology ensures more uniform and consistent ventilation of the control cabinet through higher pressure stability. Tool-free mounting
Material	Plastic
Color	RAL 7035
Supply includes	Complete unit ready to install, including pleated filter
Fan	Diagonal, EC motor
Unimpeded air flow (with pleated filter)	At 50 Hz: 1,161 m <sup>3</sup> /h At 60 Hz: 1,161 m <sup>3</sup> /h
Airflow with corresponding outlet filter including pleated filter	At 50 Hz: 969 m <sup>3</sup> /h

# Features

Unimpeded air flow (with chopped fiber filter)	At 50 Hz: 931 m <sup>3</sup> /h
Airflow with corresponding outlet filter including chopped fiber filter	At 50 Hz: 728 m <sup>3</sup> /h
Rated operating voltage	100 V - 130 V, 1~, 50 Hz/60 Hz
Rated power Pel	At 50 Hz: 174.6 W
Rated current max.	At 50 Hz: 2.52 A
Dimensions	Width: 323 mm Height: 323 mm Depth: 156 mm
Installation depth	136 mm
Mounting cut-out	Width of opening: 292 mm Cut-out height: 292 mm
Protection category IP to IEC 60529	IP 51 with chopped fiber filter/pleated filter IP52 with pleated filter and absorber mat IP 56 with chopped fiber filter/pleated filter and hose-proof hood
Protection category NEMA	Type 1, 12 with chopped fiber filter/pleated filter Type 3, 3R with chopped fiber filter/pleated filter and hose-proof hood
Pre-fuse	Miniature circuit-breaker/fuse: 6 A
Operating temperature range	-25 °C...55 °C
Storage temperature range	-25 °C...70 °C
Noise pressure level	At 50 Hz: 72 dB(A)
Interfaces	0 - 10 V/PWM input Speed output
Packaging unit	1 pc(s).
Net weight	4.17 kg
Gross weight	4.18 kg
Customs tariff number	84145915
ETIM 9	EC000320

# Features

---

ETIM 8	EC000320
ECLASS 8.0	27180716
Product description	SK Blue e+ filter fan, EC technology, 1161 m <sup>3</sup> /h, 100 V - 130 V, 1~, 50 Hz/60 Hz, WHD: 323 x 323 x 156.5 mm, RAL 7035

---

# Approvals

---

Approvals	CSA 30 - KC Korea UL + C-UL - FTTA UR + C-UR (recognized)
Explanations	Declaration of conformity

---