

Rittal – The System.

Faster – better – everywhere.



SK 3302.200

**Wall-Mounted Cooling Unit
TopTherm Blue e**

State: 2026-02-05 (Source: rittal.com/ca-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SK 3302.200 - Wall-Mounted Cooling Unit TopTherm Blue e 1023.64 - 13,648.6 BTU/h

Energy efficient Blue e wall mounting cooling units in performance classes 1023.64 to 13648.57 BTU/h, and with integrated electrical condensation evaporation for 3412.14 BTU/h and above. Available in the special formats "horizontal" and "flat".



Features

Model No.	SK 3302.200
Version	wall-mounted
Product description	Energy efficient Blue e wall-mounted cooling units in performance classes 300 W to 4000 W and with integrated electrical condensation evaporation for 1000 W and above.
Benefits	May be linked to the IoT interface via the Blue e IoT adapter for cooling units with an output of 500 W or higher and e-comfort controllers
Material	Stainless steel 1.4301 (AISI 304)
Color	RAL 9007
Supply includes	Condenser with hydrophobic RiNano coating Wired ready for connection (plug-in terminal strip) Drilling template Fasteners
Total cooling output to DIN EN 14511	Cooling output L35 L35/50 Hz: 0.31 kW Cooling output L35 L35/60 Hz: 0.33 kW Cooling output L35 L50/50 Hz: 0.15 kW Cooling output L35 L50/60 Hz: 0.18 kW

Features

Rated operating voltage	230 V, 1~, 50 Hz/60 Hz
Rated current max.	At 50 Hz: 1.6 A
	At 60 Hz: 1.7 A
Start-up current (max.)	At 50 Hz: 3 A
	At 60 Hz: 3.4 A
Air throughput (unimpeded air flow)	External circuit: 310 m ³ /h
	Internal circuit: 345 m ³ /h
Energy efficiency ratio (EER) 50/60 Hz L35 L35	Refrigeration factor L35 L35 (EER) 50 Hz: 1.07
	Refrigeration factor L35 L35 (EER) 60 Hz: 1.06
Version	wall-mounted
Dimensions	Width: 280 mm
	Height: 550 mm
	Depth: 140 mm
Protection category IP to EN 60 529	External circuit, IP 34
	Internal circuit, IP 54
Protection category NEMA	UL Type 12
Refrigerant/cooling medium	Refrigerant: R-513A
	Quantity: 0.11 kg
	Global Warming Potential (GWP): 631
	CO ₂ equivalent (CO ₂ e): 0.07 t
Temperature control	Basic controller (factory setting +35 °C)
Operating temperature range	10 °C...50 °C
Operating temperature max @60 Hz	50 °C
Storage temperature range	-40 °C...70 °C
Setting range	30 °C...50 °C
Rated power Pel	Rated power L35 L35/50 Hz: 0.29 kW
	Rated power L35 L35/60 Hz: 0.31 kW
	Rated power L35 L50/50 Hz: 0.32 kW
	Rated power L35 L50/60 Hz: 0.33 kW
Permissible operating pressure (p. max.)	25 bar

Features

Pre-fuse	Miniature circuit-breaker/fuse: 10 A
Note on Model No.:	Delivery times on request.
Packaging unit	1 pc(s).
Net weight	12
Gross weight	12.28
Customs tariff number	84158200
EAN	4028177379602
ETIM 9	EC000855
ETIM 8	EC000855
ECLASS 8.0	27180704

Approvals

Approvals	UL + C-UL (listed) UL + C-UL - FTTA UR + C-UR (recognized)
Certificates	EAC
Explanations	Declaration of conformity Declaration of conformity UK
