

Rittal – The System.

Faster – better – everywhere.



SK 3311.148 Liquid Cooling Package

State: 2026-06-04 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3311.148 - Liquid Cooling Package LCP Inline CW

These highly efficient Inline units can create a cold curtain down a row rather than simply moving air into an aisle. Available in two versions: Flush, a configuration where the unit's face matches that of the adjacent enclosures and air flows into the racks, and Protruding where the unit is bumped out 8 inches into the aisle and cool air flows from both sides across the face of nearby enclosures. The unit's high-efficiency fans have been moved to the front of the LCP – on the cool side away from maximum heat – which will extend the life of the fans. Water connections are available at either the top or bottom of the unit.



Features

Model No.	SK 3311.148
Benefits	<ul style="list-style-type: none">Maximum energy efficiency due to EC fan technology and IT-based controlMinimal area load due to low weightThe separation of cooling and enclosure prevents water from entering the server enclosureRedundant temperature sensor integrated at the air endFan modules configurable as n+1 redundancy.Targeted cooling output thanks to modular box-type plug-in fan unitsBy using high water inlet temperatures, the proportion of indirect free cooling is increased, which in turn reduces operating costsOptimum adaptability due to dynamic, continuous control of the cold water volume flowMinimal pressure loss at the air end, which in turn minimizes the power consumption of the fansUp to 102364.26 BTU/h cooling output on a small footprintTop or bottom feed water connection

Features

Function principle	The hot air is drawn in from the room or hot aisle at the rear of the device and expelled at the front into the cold aisle after cooling. With this product, a raised floor is not necessary
Color	Exterior: RAL 9005 Enclosure frame and interior: RAL 7035
Supply includes	Incl. 2 fan modules.
Options	Various sensors Racks
Max. cooling output	30 kW
Type of connection (electrical)	Connector
Air throughput per fan	4800
Cooling medium	Water
EC fan	Yes
Fans may be exchanged with the system operational	Yes
Cooling medium note	18/27/30 kW
Temperature control	Infinitely variable fan control 2-way control ball valve
Water connections	DN 40 (G 1½" external thread)
Monitoring	Monitoring of all system-relevant parameters such as server air intake temperature, server waste air temperature, water inlet/return temperature, water flow, cooling output, fan speed, leakage. Direct connection of the unit via SNMP over Ethernet Integration into RiZone
Installation in bayed enclosure suite	Flush
Dimensions	Width: 300 mm Height: 2,000 mm Depth: 1,050 mm
Total cooling output/number of fan modules	18 kW/2 27 kW/3 30 kW/4

Features

Water inlet temperature	15 °C
-------------------------	-------

Packaging unit	1 pc(s).
----------------	----------

Approvals

Approvals	UL
-----------	----