

Rittal – The System.

Faster – better – everywhere.



SK 3311.470 Liquid Cooling Package

State: 2026-04-06 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3311.470 - Liquid Cooling Package LCP Inline DX

Ideal for cooling small and medium-sized IT applications. Continuous adjustments of the cooling output provided by output-controlled compressors in the Inline DX LCP (evaporator). An external condenser is required to operate the unit.



Features

Model No.	SK 3311.470
Version	LCP Inline DX
Benefits	<ul style="list-style-type: none">Maximum energy efficiency due to EC fan technology and IT-based controlMinimal pressure loss at the air end, which in turn minimizes the power consumption of the fansTemperature monitoring and control.Redundant temperature sensor integrated at the air endDue to the speed-regulated compressor, the cooling output adapts to the actual requirementsSpecial maintenance of the LCP DX due to separation of cooling and server enclosuresUsing LCP DX/FC variants in combination with indirect free cooling helps to save operating costs
Applications	<ul style="list-style-type: none">Ideal for IT cooling of small and medium-sized locationsOne or two racks can be cooled separately

Features

Function principle	<p>LCP for use within a bayed enclosure suite. Hot air is drawn in from the aisle at the rear of the device, cooled by the high-capacity compact impellers, and blown back into the room or cold aisle after cooling</p> <p>The LCP DX/FC versions contain both refrigerant as well as a water/glycol heat exchanger. A free cooler is also integrated in the external condenser.</p> <p>Absorbed thermal energy is emitted to the ambient air at the external condenser location, without heating up the installation room</p>
Material	Carbon steel, spray finished
Options	Humidifier Dehumidification and reheater Condensate lift pump Low-temperature/high-temperature condenser (-40 °C/+53 °C)
Version	Row Cooling
Monitoring	Direct connection of the unit via SNMP over Ethernet Integration into RiZone
Note	Variant with UL approval available on request
Total cooling output to DIN EN 14511	Useful cooling output L30 L22: 35 kW
Total cooling output/number of fan modules	35 kW/3
Modulation range	8 - 35 kW
Air throughput (unimpeded air flow)	At 50 Hz: 9,900 m ³ /h
Dimensions	Width: 600 mm Height: 2,000 mm Depth: 1,200 mm
Suitable for enclosure type	TS IT
Installation in bayed enclosure suite	Flush
Rated operating voltage	380 V - 480 V, 3~, 60 Hz 400 V, 3~, 50 Hz

Features

Rated current max.	At 50 Hz: 22.4 A
Max. cooling output	35 kW
Type of connection (electrical)	Connection clamp
Duty cycle	100 %
Cooling medium	Refrigerant
EC fan	Yes
SNMP card	Yes
Fans may be exchanged with the system operational	Yes
Temperature control	Ininitely variable fan control 2-way control ball valve
Pre-fuse	Miniature circuit-breaker/fuse: 40 A
Operating temperature range	15 °C...35 °C
Noise pressure level	At 50 Hz: 69 dB(A)
Protection category IP to EN 60 529	IP 40
Options	Humidifier Dehumidification and reheater Condensate lift pump Low-temperature/high-temperature condenser (-40 °C/+53 °C)
Packaging unit	1 pc(s).
Net weight	315 kg
Gross weight	325 kg
Customs tariff number	84158200
ETIM 9	EC002515
ETIM 8	EC002515
ECLASS 8.0	27180712
Product description	Evaporator unit for suite cooling in conjunction with condenser 3311.370, RAL 7035

Approvals

Explanations

Declaration of conformity