Rittal - The System.

Faster – better – everywhere.



SK 3312.570 Liquid Cooling Package

State: 2025-11-06 (Source: rittal.com/ca-en)



SK 3312.570 - Liquid Cooling Package LCP Inline CW, LCP Inline CWG

Bayed climate control designed for siting within a bayed enclosure suite. The hot air is extracted at the rear of the unit, cooled and then expelled forwards to the cold aisle.

Features

Model No.	SK 3312.570
Benefits	Maximum energy efficiency due to EC fan technology and IT-based control
	Minimal pressure loss at the air end, which in turn minimizes the power consumption of the fans
	Optimum adaptability due to dynamic, continuous control of the cold water volume flow
	By using high water inlet temperatures, the proportion of indirect
	free cooling is increased, which in turn reduces operating costs Targeted cooling output thanks to modular fan units
	Fan modules configurable as n+1 redundancy.
	Standard 3-phase connection for electrical redundancy
	Redundant temperature sensor integrated at the air end
	The separation of cooling and enclosure prevents water from entering the server enclosure
	A maximum floor area of 0.36 m ² for all cooling services
	Improved heat recovery due to high water return temperatures wher
	using the LCP CW glycol variants, for example in conjunction with a heat pump
	Optimum access for maintenance and service from the front and the rear
	Tool-free fan module replacement
Function principle	The hot air is drawn in from the room or hot aisle at the rear of the
	device and expelled at the front into the cold aisle after cooling.
	With this product, a raised floor is not necessary
Material	Carbon steel, spray finished
Color	RAL 7035
Options	Direct connection of additional CMC III sensors is also possible Racks 2200 mm high

© Rittal 2025

2

Features

Version	Row Cooling
Monitoring	Monitoring of all system-relevant parameters such as server air intake temperature, server waste air temperature, water inlet/return temperature, water flow, cooling output, fan speed, leakage. Direct connection of the unit via SNMP over Ethernet Integration into RiZone
Total cooling output/number of fan modules	30 kW/4 32 kW/5 35 kW/6
Air throughput (unimpeded air flow)	At 50 Hz: 4,800 m³/h
Number of fan modules in supplied state	4
Dimensions	Width: 300 mm Height: 2,000 mm Depth: 1,200 mm
Installation in bayed enclosure suite	Protruded
Rated operating voltage	230 V, 1~, 50 Hz/60 Hz 400 V, 3~, 50 Hz/60 Hz
Max. cooling output	35 kW
Type of connection (electrical)	Connector
Duty cycle	100 %
Cooling medium	Water/glycol
EC fan	Yes
Fans may be exchanged with the system operational	Yes
Temperature control	Infinitely variable fan control 2-way control ball valve
Water connections	DN 40 (G 1½" external thread)
Permissible operating pressure (p. max.)	10 bar

© Rittal 2025 3

Features

Water inlet temperature	15 °C
Protection category IP to EN 60 529	IP 20
Optimized condensate management even at low water flow temperatures	Yes
Options	Direct connection of additional CMC III sensors is also possible Racks 2200 mm high
Packaging unit	1 pc(s).
Net weight	241
Gross weight	260
EAN	4028177811614
ETIM 9	EC002515
ETIM 8	EC002515
ECLASS 8.0	27180712

Approvals

|--|

© Rittal 2025