

Rittal – The System.

Faster – better – everywhere.



SK 3311.360 Condenser Unit

State: 2025-07-15 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3311.360 - Condenser Unit For LCP DX

The condenser units are needed for operating refrigerant-based LCPs. Depending on the version, the units have an external condenser and ventilator or an additional free cooler. The version with the free cooler is required for the LCP DX/FC combination version. The units are suitable for roof or wall mounting.

Features

Model No.	SK 3311.360
Version	Condensers
Product description	The condenser unit is needed to operate the refrigerant-based LCPs, and comprises the external condenser and two fans that are speed-controlled by means of pressure in the cooling circuit.
Material	Carbon steel, spray finished
Surface finish	Powder-coated, galvanized
Color	RAL 9003
Supply includes	Assembly parts
Max. cooling output	12 kW
Temperature control	Speed-Controlled Fan
Refrigerant/cooling medium	Refrigerant: R410A Cooling medium: -
Dimensions	Width: 1,303 mm Height: 915 mm Depth: 620 mm
Total cooling output/number of fan modules	2
Rated operating voltage	230 V, 1~, 50 Hz/60 Hz
Packaging unit	1 pc(s).
Net weight	50
Gross weight	50

Features

Customs tariff number	84189910
EAN	4028177691438
ETIM 9	EC002515
ETIM 8	EC002515
ECLASS 8.0	27180712

Approvals

Certificates	EAC
--------------	-----