Rittal – The System.

Faster – better – everywhere.





SK 3313.530 Liquid Cooling Package

State: 2025-12-14 (Source: rittal.com/ca-en)



SK 3313.530 - Liquid Cooling Package LCP Inline CW, LCP Inline CWG

Bayed climate control designed for siting within a bayed enclosure suite. The hot air is extracted at the rear of the unit, cooled and then expelled forwards to the cold aisle.

Features

Model No.	SK 3313.530
Version	CW
Benefits	Maximum energy efficiency due to EC fan technology and IT-based control
	Minimal pressure loss at the air end, which in turn minimizes the power consumption of the fans
	Optimum adaptability due to dynamic, continuous control of the cold water volume flow
	By using high water inlet temperatures, the proportion of indirect free cooling is increased, which in turn reduces operating costs Targeted cooling output thanks to modular fan units Fan modules configurable as n+1 redundancy. Standard 3-phase connection for electrical redundancy
	Redundant temperature sensor integrated at the air end The separation of cooling and enclosure prevents water from entering the server enclosure
	A maximum floor area of 0.36 m ² for all cooling services Improved heat recovery due to high water return temperatures when using the LCP CW glycol variants, for example in conjunction with a heat pump
	Optimum access for maintenance and service from the front and the rear Tool-free fan module replacement
Function principle	The hot air is drawn in from the room or hot aisle at the rear of the device and expelled at the front into the cold aisle after cooling. With this product, a raised floor is not necessary
Material	Carbon steel, spray finished
Color	RAL 7035

© Rittal 2025

2

Features

Options	Direct connection of additional CMC III sensors is also possible Racks 2200 mm high	
Version	Row Cooling	
Monitoring	Monitoring of all system-relevant parameters such as server air intake temperature, server waste air temperature, water inlet/retu temperature, water flow, cooling output, fan speed, leakage. Direct connection of the unit via SNMP over Ethernet Integration into RiZone	
Total cooling output/number of fan modules	10 kW/1 20 kW/2 30 kW/3	
Air throughput (unimpeded air flow)	At 50 Hz: 4,800 m³/h	
Number of fan modules in supplied state	1	
Dimensions	Width: 300 mm Height: 2,000 mm Depth: 1,200 mm	
Suitable for enclosure type	VX IT	
Installation in bayed enclosure suite	Protruded	
Rated operating voltage	230 V, 1~, 50 Hz/60 Hz 400 V, 3~, 50 Hz/60 Hz	
Max. cooling output	30 kW	
Type of connection (electrical)	Connector	
Duty cycle	100 %	
Cooling medium	Water	
Cooling medium note	Water quality according to unit specifications.	
EC fan	Yes	
Fans may be exchanged with the system operational	Yes	

© Rittal 2025 3

Features

Temperature control	Infinitely variable fan control 2-way control ball valve	
Water connections	DN 40 (G 1½" external thread)	
Permissible operating pressure (p. max.)	10 bar	
Water inlet temperature	15 °C	
Protection category IP to EN 60 529	IP 20	
Options	Direct connection of additional CMC III sensors is also possible Racks 2200 mm high	
Packaging unit	1 pc(s).	
Net weight	200	
Gross weight	209.5	
Customs tariff number	84186900	
EAN	4028177953918	
ETIM 9	EC002515	
ETIM 8	EC002515	
ECLASS 8.0	27180712	

Approvals

Explanations	Declaration of conformity	

© Rittal 2025