

# Rittal – The System.

Faster – better – everywhere.



## SK 3313.250

## Liquid Cooling Package

State: 2026-01-30 (Source: [rittal.com/ca-en](https://rittal.com/ca-en))



FRIEDHELM LOH GROUP

# SK 3313.250 - Liquid Cooling Package LCP Rack CW, LCP Rack CWG

Cooling via high-performance compact impellers. The LCP draws in air from the side at the rear of the server enclosure and blows the cooled air back into the front part of the server enclosure from the side.

## Features

Model No.	SK 3313.250
Version	CWG
Benefits	<p>Maximum energy efficiency due to EC fan technology and IT-based control</p> <p>Minimal pressure loss at the air end, which in turn minimizes the power consumption of the fans</p> <p>Control of the server inlet temperature</p> <p>Redundant temperature sensor integrated at the air end</p> <p>Optimum adaptability due to dynamic, continuous control of the cold water volume flow</p> <p>By using high water inlet temperatures, the proportion of indirect free cooling is increased, which in turn reduces operating costs</p> <p>Targeted cooling output thanks to modular fan units</p> <p>Fan modules configurable as n+1 redundancy.</p> <p>Standard 3-phase connection for electrical redundancy</p> <p>The separation of cooling and enclosure prevents water from entering the server enclosure</p> <p>A maximum floor area of 0.36 m<sup>2</sup> for all cooling services</p> <p>Improved heat recovery due to high water return temperatures when using the LCP CW glycol variants, for example in conjunction with a heat pump</p> <p>Optimum access for maintenance and service from the front and the rear</p> <p>Tool-free fan module replacement</p>
Function principle	The LCP draws in the air at the sides at the rear of the server enclosures, cools it using high-performance compact impellers, and blows the cooled air back into the front part of the server enclosure at the sides

# Features

Material	Carbon steel, spray finished
Color	RAL 7035
Options	<p>Fully integrated fire detection and extinguisher system</p> <p>Automatic server enclosure door opening</p> <p>Direct connection of additional CMC III sensors is also possible</p> <p>Racks 2200 mm high</p>
Version	Rack cooling
Monitoring	<p>Monitoring of all system-relevant parameters such as server air intake temperature, server waste air temperature, water inlet/return temperature, water flow, cooling output, fan speed, leakage.</p> <p>Direct connection of the unit via SNMP over Ethernet</p> <p>Integration into RiZone</p>
Total cooling output/number of fan modules	<p>38 kW/4</p> <p>40 kW/5</p> <p>44 kW/6</p>
Air throughput (unimpeded air flow)	At 50 Hz: 4,800 m <sup>3</sup> /h
Number of fan modules in supplied state	4
Dimensions	<p>Width: 300 mm</p> <p>Height: 2,000 mm</p> <p>Depth: 1,200 mm</p>
Suitable for enclosure type	VX IT
Installation in bayed enclosure suite	Flush
Rated operating voltage	<p>200 V - 240 V, 1~, 60 Hz</p> <p>346 V - 415 V, 3~, 50 Hz</p> <p>346 V - 415 V, 3~, 60 Hz</p>
Max. cooling output	35 kW
Type of connection (electrical)	Connector
Duty cycle	100 %
Cooling medium	Water/glycol

# Features

EC fan	Yes
Fans may be exchanged with the system operational	Yes
Temperature control	Infinitely variable fan control 2-way control ball valve
Water connections	DN 40 (G 1½" external thread)
Permissible operating pressure (p. max.)	10 bar
Water inlet temperature	15 °C
Protection category IP to EN 60 529	IP 20
Optimized condensate management even at low water flow temperatures	Yes
Options	Fully integrated fire detection and extinguisher system Automatic server enclosure door opening Direct connection of additional CMC III sensors is also possible Racks 2200 mm high
Packaging unit	1 pc(s).
Net weight	203
Gross weight	253
Customs tariff number	84186900
EAN	4028177953895
ETIM 9	EC002515
ETIM 8	EC002515
ECLASS 8.0	27180712

# Approvals

# Approvals

---

Explanations

Declaration of conformity