


Rittal – The System.

Faster – better – everywhere.



SK 3313.568 Liquid Cooling Package

State: 2025-09-16 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3313.568 - Liquid Cooling Package LCP Inline CW, LCP Inline CWG

Bayed climate control designed for siting within a bayed enclosure suite. The hot air is extracted at the rear of the unit, cooled and then expelled forwards to the cold aisle.



Features

| | |
|--------------------|---|
| Model No. | SK 3313.568 |
| Version | CW |
| Benefits | <p>Maximum energy efficiency due to EC fan technology and IT-based control</p> <p>Minimal pressure loss at the air end, which in turn minimizes the power consumption of the fans</p> <p>Optimum adaptability due to dynamic, continuous control of the cold water volume flow</p> <p>By using high water inlet temperatures, the proportion of indirect free cooling is increased, which in turn reduces operating costs</p> <p>Targeted cooling output thanks to modular fan units</p> <p>Fan modules configurable as n+1 redundancy.</p> <p>Redundant temperature sensor integrated at the air end</p> <p>The separation of cooling and enclosure prevents water from entering the server enclosure</p> <p>A maximum floor area of 0.36 m² for all cooling services</p> <p>Optimum access for maintenance and service from the front and the rear</p> <p>Tool-free fan module replacement</p> |
| Function principle | <p>The hot air is drawn in from the room or hot aisle at the rear of the device and expelled at the front into the cold aisle after cooling.</p> <p>With this product, a raised floor is not necessary</p> |
| Material | Carbon steel, spray finished |

Features

| | |
|--|--|
| Surface finish | RAL 9005, fine structure matt |
| Color | RAL 9005 |
| Options | Direct connection of additional CMC III sensors is also possible Racks 2200 mm high |
| Version | Row Cooling |
| Monitoring | Monitoring of all system-relevant parameters such as server air intake temperature, server waste air temperature, water inlet/return temperature, water flow, cooling output, fan speed, leakage. Direct connection of the unit via SNMP over Ethernet Integration into RiZone |
| Total cooling output/number of fan modules | 48 kW/4 51 kW/5 53 kW/6 |
| Air throughput (unimpeded air flow) | At 60 Hz: 8,000 m³/h |
| Number of fan modules in supplied state | 6 |
| Dimensions | Width: 300 mm Height: 2,000 mm Depth: 1,200 mm |
| Suitable for enclosure type | VX IT TS IT PRO |
| Installation in bayed enclosure suite | Protruded |
| Rated operating voltage | 200 V - 240 V, 1~, 50 Hz/60 Hz 200 - 240 V AC |
| Max. cooling output | 53 kW |
| Type of connection (electrical) | Connector |
| Duty cycle | 100 % |
| Cooling medium | Water |
| Cooling medium note | Water quality according to unit specifications. |
| EC fan | Yes |

Features

| | |
|---|--|
| Fans may be exchanged with the system operational | Yes |
| Temperature control | Infinitely variable fan control 2-way control ball valve |
| Water connections | DN 40 (G 1½" external thread) |
| Permissible operating pressure (p. max.) | 10 bar |
| Water inlet temperature | 15 °C |
| Protection category IP to EN 60 529 | IP 20 |
| Options | Direct connection of additional CMC III sensors is also possible Racks 2200 mm high |
| Packaging unit | 1 pc(s). |
| Net weight | 228 |
| Gross weight | 240 |
| Customs tariff number | 84186900 |
| EAN | 4028177962774 |
| ETIM 9 | EC002515 |
| ETIM 8 | EC002515 |
| ECLASS 8.0 | 27180712 |

Approvals

| | |
|-----------|------------------------|
| Approvals | UR + C-UR (recognized) |
|-----------|------------------------|