

Rittal – The System.

Faster – better – everywhere.



SK 3328.504

TopTherm Blue e Wall-Mounted Cooling Unit, NEMA 4X

State: 2026-06-28 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3328.504 - TopTherm Blue e Wall-Mounted Cooling Unit, NEMA 4X 1706.07 - 8530.36 BTU/h

Energy-efficient Blue e wall-mounted cooling units in power categories 1706.07 - 8530.36 BTU/h with e-Comfort controller integrated as standard and electrical condensate evaporation. Protection category NEMA 4X.



Features

Model No.	SK 3328.504
Version	wall-mounted
Product description	Energy-efficient Blue e wall-mounted cooling units with integral e-Comfort controller and electric condensate evaporation as standard. Protection category NEMA 4X.
Benefits	May be linked to the IoT interface via the Blue e IoT adapter for cooling units with an output of 500 W or higher and e-comfort controllers
Material	Stainless steel 1.4404 (AISI 316L)
Color	RAL 7001
Supply includes	Condenser with hydrophobic RiNano coating Wired ready for connection (plug-in terminal strip) Drilling template Fasteners Integral electric condensate evaporation

Features

Total cooling output to DIN EN 14511	Cooling output L35 L35/50 Hz: 2.1 kW Cooling output L35 L35/60 Hz: 2.39 kW Cooling output L35 L50/50 Hz: 1.52 kW Cooling output L35 L50/60 Hz: 1.76 kW
Rated operating voltage	230 V, 1~, 50 Hz/60 Hz
Rated current max.	At 50 Hz: 5.8 A At 60 Hz: 6.8 A
Start-up current (max.)	At 50 Hz: 20 A At 60 Hz: 22 A
Air throughput (unimpeded air flow)	External circuit: 980 m ³ /h Internal circuit: 980 m ³ /h
Energy efficiency ratio (EER) 50/60 Hz L35 L35	Refrigeration factor L35 L35 (EER) 50 Hz: 2.44 Refrigeration factor L35 L35 (EER) 60 Hz: 2.21
Version	wall-mounted
Dimensions	Width: 405 mm Height: 1,650 mm Depth: 388 mm
Protection category IP to EN 60 529	External circuit, IP 34 Internal circuit IP 55
Protection category NEMA	NEMA 4X
Refrigerant/cooling medium	Refrigerant: R-513A Quantity: 0.9 kg Global Warming Potential (GWP): 631 CO ₂ equivalent (CO ₂ e): 0.57 t
Temperature control	e-Comfort Controller (factory setting +35 °C)
Operating temperature range	10 °C...50 °C
Storage temperature range	-40 °C...70 °C
Setting range	20 °C...50 °C
Rated power Pel	Rated power L35 L35/50 Hz: 0.86 kW Rated power L35 L35/60 Hz: 1.08 kW Rated power L35 L50/50 Hz: 1.02 kW Rated power L35 L50/60 Hz: 1.23 kW

Features

Permissible operating pressure (p. max.)	28 bar
Pre-fuse	Miniature circuit-breaker/fuse: 16 A
Packaging unit	1 pc(s).
Net weight	80 kg
Gross weight	95.5 kg
Customs tariff number	84158200
ETIM 9	EC000855
ETIM 8	EC000855
ECLASS 8.0	27180704
Product description	SK cooling unit Blue e, wall-mounted, 7506 BTU/h, 230 V, 1~, 50/60 Hz, Stainless steel, WHD: 405 x 1650 x 388 mm

Approvals

Approvals	UL + C-UL (listed) UL + C-UL - FTFA UR + C-UR (recognized)
Explanations	FCC Declaration of conformity Declaration of conformity - F-gas regulation Declaration of conformity UK
