

# Rittal – The System.

Faster – better – everywhere.



## SK 3334.400

### Blue e+ chiller

State: 2026-02-09 (Source: [rittal.com/ca-en](https://rittal.com/ca-en))



FRIEDHELM LOH GROUP

# SK 3334.400 - Blue e+ chiller 5118.2 - 23,898 BTU/h

Blue e+ chillers are efficient, flexible and compact. The cooling water is centrally cooled, supplying the air/water heat exchanger and other systems an efficient cooling solution. Up to 70% energy saved due to speed-regulated components and inverter technology. International approvals and multi-voltage capability for worldwide use. Intuitive operation using touch display and intelligent communication interfaces ensure convenient operation and analysis.

## Features

Model No.	SK 3334.400
Benefits	<p>Blue e+ chillers ensure central and efficient cooling of liquid media with a high level of temperature precision and innovative DC inverter technology</p> <p>Suitable for international use due to its unique multi-voltage capability (without rewiring) and high operating limits</p> <p>Maximum safety due to integrated overflow valve and monitoring sensors</p> <p>Intuitive operation due to touch display and intelligent interfaces</p> <p>Compact and modular layout ensures minimum footprint</p> <p>Pumps with highly-efficient IE3 motors</p>
Color	Textured RAL 7035
Supply includes	<p>Complete unit ready for connection (plug-in terminal strip)</p> <p>Multilingual documentation</p>
Options	<p>For remote monitoring and networking of cooling units and chillers, use the Blue e+ Generation IoT Interface, item number 3124.300.</p> <p>Increase machine availability and process safety by remote monitoring of device data, condition, and system messages.</p>
Protection category IP to EN 60 529	<p>IP 24</p> <p>IP 54 (electrics)</p>
Total cooling output Tw10 / Tu32	<p>Cooling output Tw10 Tu32/50 Hz: 4.33 kW</p> <p>Cooling output Tw10 Tu32/60 Hz: 4.23 kW</p>
Total cooling output Tw18 / Tu32	<p>Cooling output Tw18 Tu32/50 Hz: 5.72 kW</p> <p>Cooling output Tw18 Tu32/60 Hz: 5.62 kW</p>
Total cooling output to DIN EN 14511 Tw18 / Tu35	<p>Cooling output Tw18 Tu35/50 Hz: 5.5 kW</p> <p>Cooling output Tw18 Tu35/60 Hz: 5.4 kW</p>

# Features

Air throughput (unimpeded air flow)	At 50 Hz: 1,850 m <sup>3</sup> /h At 60 Hz: 1,850 m <sup>3</sup> /h
Rated operating voltage	380 V - 415 V, 3~, 50 Hz 440 V - 480 V, 3~, 60 Hz
Dimensions	Width: 450 mm Height: 1,020 mm Depth: 710 mm
Note	When the software is downloaded, a contract is concluded between the contractual partner and Rittal for the free use of the software in accordance with these license conditions.
Temperature control	e+ controller (factory setting +20 °C)
Operating temperature range	-5 °C...50 °C
Storage temperature range	-40 °C...70 °C
Operating temperature range of cooling medium	5 °C...35 °C
Temperature hysteresis	± 0.5 K
Refrigerant/cooling medium	Refrigerant: R-513A Quantity: 1.2 kg Global Warming Potential (GWP): 631 CO <sub>2</sub> equivalent (CO <sub>2</sub> e): 0.76 t
Pump pressure	At 50 Hz: 2.9 bar
Volumetric flow (cooling medium)	At 50 Hz: 15 l/min
Rated power Pel	At 50 Hz: 2.63 kW At 60 Hz: 2.9 kW
Rated current max.	At 50 Hz: 4 A At 60 Hz: 3.8 A
Pre-fuse	Miniature circuit-breaker/fuse: 16 A
Refrigeration factor (EER) 50 Hz Tw18 / Tu35 DIN EN 14511	2.16
Water circuit	hermetically open
Water connections	¾" internal thread

# Features

---

Number of cooling circuits	1
Tank	Material: Plastic PE Volume: 12 l
Packaging unit	1 pc(s).
Net weight	96
Gross weight	115
Customs tariff number	84186900
EAN	4028177809857
ETIM 9	EC002516
ETIM 8	EC002516
ECLASS 8.0	27180713

---

# Approvals

---

Approvals	IEC CB UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity - F-gas regulation

---