Rittal - The System.

Faster – better – everywhere.





SK 3336.450 Blue e chiller

State: 2025-12-14 (Source: rittal.com/ca-en)



SK 3336.450 - Blue e chiller 27,297.14 - 163,782.82 BTU/h

The Blue e chiller fitted in the enclosure provides central and economical water cooling. The microchannel technology enables a reduction in the coolant quantity. Intuitive operation via a touch display and intelligent communication interfaces ensure convenient operation and analysis. The safety functions integrated in the standard version mean maximum safety. The delivery time is also reduced thanks to the predefined options package.

Features

| Model No. | SK 3336.450 |
|---|--|
| Version | Robust industrial standard Floating contact for collective fault signal |
| Benefits | Coolant quantity reduced through the use of microchannel technology Touch-display for easy user handling Remote monitoring already integrated in the basic unit Integrated safety functions Pre-configured options |
| Color | Housing: RAL 7035 Base/Plinth: RAL 7016 |
| Supply includes | Chiller wired ready for connection Multilingual documentation including functional diagram and wiring plans |
| Protection category IP to EN 60 529 | IP 44 (electrics) |
| Total cooling output to DIN EN 14511 Tw18 / Tu35 | Cooling output Tw18 Tu35/50 Hz: 24 kW Cooling output Tw18 Tu35/60 Hz: 26 kW |
| Air throughput (unimpeded air flow) | At 50 Hz: 12,000 m³/h At 60 Hz: 14,500 m³/h |
| Rated operating voltage | 400 V, 3~, 50 Hz 460 V, 3~, 60 Hz |
| Dimensions | Width: 760 mm Height: 1,265 mm Depth: 1,515 mm |

© Rittal 2025 2

Features

| 76 dB(A) |
|---|
| 10 °C43 °C |
| 10 °C25 °C |
| ± 2 K |
| Refrigerant: R-513A Quantity: 3.4 kg Global Warming Potential (GWP): 631 CO2 equivalent (CO2e): 2.15 t |
| At 50 Hz: 2 bar At 60 Hz: 3.6 bar |
| At 50 Hz: 70 I/min At 60 Hz: 75 I/min |
| At 50 Hz: 11.48 kW At 60 Hz: 14.43 kW |
| At 50 Hz: 24.3 A At 60 Hz: 24.5 A |
| R 1¼" internal thread |
| 1 |
| Material: Plastic PE Volume: 78 I |
| 414 kg |
| 1 pc(s). |
| 298 |
| 350 |
| 84186900 |
| 4028177817456 |
| EC002516 |
| EC002516 |
| 27180713 |
| |

© Rittal 2025 3

Approvals

Explanations

Declaration of conformity Declaration of conformity - F-gas regulation

© Rittal 2025