

Rittal – The System.

Faster – better – everywhere.



SK 3336.480

Blue e chiller

State: 2026-02-12 (Source: rittal.com/ca-en)



FRIEDHELM LOH GROUP

SK 3336.480 - Blue e chiller 27,297.14 - 163,782.82 BTU/h

The Blue e chiller fitted in the enclosure provides central and economical water cooling. The microchannel technology enables a reduction in the coolant quantity. Intuitive operation via a touch display and intelligent communication interfaces ensure convenient operation and analysis. The safety functions integrated in the standard version mean maximum safety. The delivery time is also reduced thanks to the predefined options package.

Features

Model No.	SK 3336.480
Version	Robust industrial standard Floating contact for collective fault signal
Benefits	Coolant quantity reduced through the use of microchannel technology Touch-display for easy user handling Remote monitoring already integrated in the basic unit Integrated safety functions Pre-configured options
Color	Housing: RAL 7035 Base/Plinth: RAL 7016
Supply includes	Chiller wired ready for connection Multilingual documentation including functional diagram and wiring plans
Protection category IP to EN 60 529	IP 44 (electrics)
Total cooling output to DIN EN 14511 Tw18 / Tu35	Cooling output Tw18 Tu35/50 Hz: 44.7 kW Cooling output Tw18 Tu35/60 Hz: 50.5 kW
Air throughput (unimpeded air flow)	At 50 Hz: 12,000 m ³ /h At 60 Hz: 14,500 m ³ /h
Rated operating voltage	400 V, 3~, 50 Hz 460 V, 3~, 60 Hz
Dimensions	Width: 900 mm Height: 1,733 mm Depth: 1,800 mm

Features

Noise pressure level	78 dB(A)
Operating temperature range	10 °C...43 °C
Operating temperature range of cooling medium	10 °C...25 °C
Temperature hysteresis	± 2 K
Refrigerant/cooling medium	Refrigerant: R-513A Quantity: 5.2 kg Global Warming Potential (GWP): 631 CO ₂ equivalent (CO ₂ e): 3.3 t
Pump pressure	At 50 Hz: 2.2 bar At 60 Hz: 3.3 bar
Volumetric flow (cooling medium)	At 50 Hz: 130 l/min At 60 Hz: 145 l/min
Rated power Pel	At 50 Hz: 22.36 kW At 60 Hz: 27.06 kW
Rated current max.	At 50 Hz: 46 A At 60 Hz: 44.9 A
Water connections	R 1½" internal thread
Number of cooling circuits	2
Tank	Material: Stainless steel AISI304 - 1.4301 (V2A) Volume: 185 l
Operating weight	720 kg
Packaging unit	1 pc(s).
Net weight	574
Gross weight	576.5
Customs tariff number	84186900
EAN	4028177974555
ETIM 9	EC002516
ETIM 8	EC002516
ECLASS 8.0	27180713

Approvals

Explanations

Declaration of conformity

Declaration of conformity - F-gas regulation