

Rittal – The System.

Faster – better – everywhere.



SK 3361.540

Wall-Mounted Cooling Unit TopTherm Blue e

State: 2026-05-09 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3361.540 - Wall-Mounted Cooling Unit TopTherm Blue e 1023.64 - 13,648.6 BTU/h

Energy efficient Blue e wall mounting cooling units in performance classes 1023.64 to 13648.57 BTU/h, and with integrated electrical condensation evaporation for 3412.14 BTU/h and above. Available in the special formats “horizontal” and “flat”.



Features

Model No.	SK 3361.540
Version	wall-mounted
Product description	Energy efficient Blue e wall-mounted cooling units in performance classes 300 W to 4000 W and with integrated electrical condensation evaporation for 1000 W and above.
Benefits	May be linked to the IoT interface via the Blue e IoT adapter for cooling units with an output of 500 W or higher and e-comfort controllers
Material	Carbon steel
Color	RAL 7035
Supply includes	Condenser with hydrophobic RiNano coating Wired ready for connection (plug-in terminal strip) Drilling template Fasteners External toroidal core transformer
Total cooling output to DIN EN 14511	Cooling output L35 L35/50 Hz: 0.82 kW Cooling output L35 L35/60 Hz: 0.82 kW Cooling output L35 L50/50 Hz: 0.59 kW Cooling output L35 L50/60 Hz: 0.6 kW

Features

Rated operating voltage	400 V, 2~, 50 Hz/60 Hz
Note on Model No.:	The technical specifications for the wall-mounted cooling unit 3361.x40 are valid with a connected external transformer
Rated current max.	At 50 Hz: 1.2 A At 60 Hz: 1.4 A
Start-up current (max.)	At 50 Hz: 6 A At 60 Hz: 6.9 A
Air throughput (unimpeded air flow)	External circuit: 550 m ³ /h Internal circuit: 230 m ³ /h
Energy efficiency ratio (EER) 50/60 Hz L35 L35	Refrigeration factor L35 L35 (EER) 50 Hz: 1.95 Refrigeration factor L35 L35 (EER) 60 Hz: 1.78
Version	wall-mounted
Dimensions	Width: 280 mm Height: 550 mm Depth: 280 mm
Protection category IP to EN 60529	External circuit, IP 34 Internal circuit, IP 54
Protection category NEMA	UL Type 12
Refrigerant/cooling medium	Refrigerant: R-513A Quantity: 0.28 kg Global Warming Potential (GWP): 631 CO ₂ equivalent (CO ₂ e): 0.18 t
Temperature control	e-Comfort Controller (factory setting +35 °C)
Operating temperature range	10 °C...55 °C
Operating temperature max @60 Hz	52 °C
Storage temperature range	-40 °C...70 °C
Setting range	20 °C...52 °C
Rated power Pel	Rated power L35 L35/50 Hz: 0.42 kW Rated power L35 L35/60 Hz: 0.46 kW Rated power L35 L50/50 Hz: 0.47 kW Rated power L35 L50/60 Hz: 0.5 kW

Features

Permissible operating pressure (p. max.)	28 bar
Pre-fuse	Transformer circuit-breaker: 6.3...10 A
Depth transformer	65 mm
Diameter transformer	126 mm
Packaging unit	1 pc(s).
Net weight	15.65 kg
Gross weight	27 kg
Customs tariff number	84158200
ETIM 9	EC000855
ETIM 8	EC000855
ECLASS 8.0	27180704
Product description	SK Cooling unit Blue e, wall-mounted, 2797.96 BTU/h, 400 V, 2~, 50/60 Hz, carbon steel, WHD: 280 x 550 x 280 mm

Approvals

Approvals	UL + C-UL (listed) UL + C-UL - FTTA UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity - F-gas regulation Declaration of conformity UK