

Rittal – The System.

Faster – better – everywhere.



SK 3374.504

Air-Water Heat Exchangers

State: 2026-01-18 (Source: rittal.com/ca-en)



FRIEDHELM LOH GROUP

SK 3374.504 - Air-Water Heat Exchangers wall-mounted

Output categories 1023.64 - 17060.71 BTU/h. For use in tough environments. Convenient mounting options and flexible water connection options. External mounting or full internal mounting possible.

Features

Model No.	SK 3374.504
Version	wall-mounted Water-carrying parts stainless steel (1.4571)
Product description	To be used in rough environments and temperature ranges of up to +70 °C. Convenient assembly options and flexible water connection options. Partial or full internal mounting possible.
Color	RAL 7035
Supply includes	Wired ready for connection Drilling template Sealing and assembly components
Total cooling output	L 35 W 10 at 400 l/h: 2.8 kW
Rated operating voltage	230 V, 1~, 50 Hz/60 Hz
Rated power Pel	At 50 Hz: 169 W At 60 Hz: 232 W
Rated current max.	At 50 Hz: 0.76 A At 60 Hz: 1.01 A
Permissible operating pressure (p. max.)	1 - 10 bar
Duty cycle	100 %
Cooling medium	Water (see Internet for specifications)
Water inlet temperature	1 °C...30 °C
Water connections	½" connector sleeve G ¾" external thread
Temperature control	e-Comfort Controller (factory setting +35 °C)

Features

Operating temperature range	1 °C...70 °C
Note	Integral non-return valve for version with e-Comfort controller
Dimensions	Width: 400 mm Height: 950 mm Depth: 145 mm
Note on Model No.:	Delivery times on request.
Pre-fuse	Miniature circuit-breaker/fuse: 4 A
Setting range	20 °C...55 °C
Protection category IP to EN 60 529	IP 55
Protection category NEMA	UL Type 1 UL Type 3R UL Type 12
Packaging unit	1 pc(s).
Net weight	23
Gross weight	25
Customs tariff number	84158300
EAN	4028177496125
ETIM 9	EC002515
ETIM 8	EC002515
ECLASS 8.0	27180712

Approvals

Approvals	CSA UL + C-UL - FTTA UR + C-UR (recognized)
Explanations	Declaration of conformity