# Rittal – The System.

Faster – better – everywhere.





# SK 3375.100 Air-Water Heat Exchangers

State: 2025-11-18 (Source: rittal.com/ca-en)



## SK 3375.100 - Air-Water Heat Exchangers wall-mounted

Output categories 1023.64 - 17060.71 BTU/h. For use in tough environments. Convenient mounting options and flexible water connection options. External mounting or full internal mounting possible.

#### **Features**

Model No.	SK 3375.100
Version	wall-mounted
	Water-carrying parts copper/brass (Cu/CuZn)
Product description	To be used in rough environments and temperature ranges of up to
	+70 °C. Convenient assembly options and flexible water connection
	options. Partial or full internal mounting possible.
Color	RAL 7035
Supply includes	Wired ready for connection
	Drilling template
	Sealing and assembly components
Total cooling output	L 35 W 10 at 400 l/h: 5 kW
Rated operating voltage	230 V, 1~, 50 Hz/60 Hz
Rated power Pel	At 50 Hz: 172 W
	At 60 Hz: 172 W
Rated current max.	At 50 Hz: 1.45 A
	At 60 Hz: 1.45 A
Permissible operating pressure (p. max.)	1 - 10 bar
Duty cycle	100 %
Cooling medium	Water (see Internet for specifications)
Water inlet temperature	1 °C30 °C
Water connections	½" connector sleeve
	G %" external thread
Temperature control	Basic controller (factory setting +35 °C)

© Rittal 2025 2

## Features

Operating temperature range	1 °C70 °C
Note	Integral non-return valve for version with e-Comfort controller
Dimensions	Width: 450 mm
	Height: 1,400 mm
	Depth: 220 mm
Pre-fuse	Miniature circuit-breaker/fuse: 4 A
Setting range	20 °C55 °C
Protection category IP to EN 60 529	IP 55
Protection category NEMA	UL Type 1
	UL Type 3R
	UL Type 12
Packaging unit	1 pc(s).
Net weight	45
Gross weight	45
Customs tariff number	84158300
EAN	4028177495715
ETIM 9	EC002515
ETIM 8	EC002515
ECLASS 8.0	27180712

# Approvals

Approvals	CSA
	30 - KC Korea
	UL + C-UL - FTTA
	UR + C-UR (recognized)
Explanations	Declaration of conformity

© Rittal 2025 3