

Rittal – The System.

Faster – better – everywhere.



SK 3386.540

**TopTherm Blue e Roof-Mounted
Cooling Unit**

State: 2025-08-21 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3386.540 - TopTherm Blue e Roof-Mounted Cooling Unit

Total cooling output 1706.07 - 13648.57 BTU/h

Energy-efficient Blue e roof-mounted cooling units in output categories 1706.07 - 13648.57 BTU/h with e-Comfort controller integrated as standard and electrical condensate evaporation.



Features

Model No.	SK 3386.540
Version	roof-mounted
Product description	Energy-efficient Blue e roof-mounted cooling units with integral e-Comfort controller and electric condensate evaporation as standard.
Benefits	May be linked to the IoT interface via the Blue e IoT adapter for cooling units with an output of 500 W or higher and e-comfort controllers
Material	Carbon steel
Color	RAL 7035
Supply includes	Condenser with hydrophobic RiNano coating Integral electric condensate evaporation Wired ready for connection (plug-in terminal strip) Drilling template Fasteners

Features

Total cooling output to DIN EN 14511	Cooling output L35 L35/50 Hz: 3 kW Cooling output L35 L35/60 Hz: 3.3 kW Cooling output L35 L50/50 Hz: 2.2 kW Cooling output L35 L50/60 Hz: 2.5 kW
Rated operating voltage	400 V, 3~, 50 Hz 460 V, 3~, 60 Hz
Note	Due to its low noise level, the roof-mounted cooling unit 3273.500 is also suitable for use in office applications.
Rated current max.	At 50 Hz: 3.4 A At 60 Hz: 3.4 A
Start-up current (max.)	At 50 Hz: 8 A At 60 Hz: 9 A
Air throughput (unimpeded air flow)	External circuit: 3,450 m³/h Internal circuit: 1,280 m³/h
Energy efficiency ratio (EER) 50/60 Hz L35 L35	Refrigeration factor L35 L35 (EER) 50 Hz: 2.29 Refrigeration factor L35 L35 (EER) 60 Hz: 2.13
Version	roof-mounted
Dimensions	Width: 796 mm Height: 470 mm Depth: 580 mm
Protection category IP to EN 60 529	External circuit, IP 34 Internal circuit, IP 54
Refrigerant/cooling medium	Refrigerant: R-513A Quantity: 1.6 kg Global Warming Potential (GWP): 631 CO2 equivalent (CO2e): 1.01 t
Type of connection (electrical)	Plug-in terminal strip
Duty cycle	100 %
Temperature control	e-Comfort Controller (factory setting +35 °C)
Operating temperature range	10 °C...55 °C
Storage temperature range	-40 °C...70 °C
Setting range	20 °C...55 °C

Features

Rated power Pel	Rated power L35 L35/50 Hz: 1.31 kW Rated power L35 L35/60 Hz: 1.55 kW Rated power L35 L50/50 Hz: 1.49 kW Rated power L35 L50/60 Hz: 1.76 kW
Permissible operating pressure (p. max.)	28 bar
Pre-fuse	Motor circuit-breaker: 6.3...10 A
Packaging unit	1 pc(s).
Net weight	83.7
Gross weight	84
Customs tariff number	84158200
EAN	4028177323308
ETIM 9	EC000855
ETIM 8	EC000855
ECLASS 8.0	27180704

Approvals

Approvals	30 - KC Korea UL + C-UL (listed) UL + C-UL - FTTA
Certificates	EAC
Explanations	Declaration of conformity Declaration of conformity - F-gas regulation Declaration of conformity UK