

Rittal – The System.

Faster – better – everywhere.



SK 3383.540

TopTherm Blue e Roof-Mounted Cooling Unit

State: 2026-06-25 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3383.540 - TopTherm Blue e Roof-Mounted Cooling Unit Total cooling output 1706.07 - 13648.57 BTU/h

Energy-efficient Blue e roof-mounted cooling units in output categories 1706.07 - 13648.57 BTU/h with e-Comfort controller integrated as standard and electrical condensate evaporation.



Features

Model No.	SK 3383.540
Version	roof-mounted
Product description	Energy-efficient Blue e roof-mounted cooling units with integral e-Comfort controller and electric condensate evaporation as standard.
Benefits	May be linked to the IoT interface via the Blue e IoT adapter for cooling units with an output of 500 W or higher and e-comfort controllers
Material	Carbon steel
Color	RAL 7035
Supply includes	Condenser with hydrophobic RiNano coating Integral electric condensate evaporation Wired ready for connection (plug-in terminal strip) Drilling template Fasteners

Features

Total cooling output to DIN EN 14511	Cooling output L35 L35/50 Hz: 1 kW Cooling output L35 L35/60 Hz: 1.09 kW Cooling output L35 L50/50 Hz: 0.8 kW Cooling output L35 L50/60 Hz: 0.81 kW
Rated operating voltage	400 V, 2~, 50 Hz/60 Hz
Note	Due to its low noise level, the roof-mounted cooling unit 3273.500 is also suitable for use in office applications.
Rated current max.	At 50 Hz: 1.7 A At 60 Hz: 2.2 A
Start-up current (max.)	At 50 Hz: 4.6 A At 60 Hz: 5.7 A
Air throughput (unimpeded air flow)	External circuit: 1,600 m ³ /h Internal circuit: 491 m ³ /h
Energy efficiency ratio (EER) 50/60 Hz L35 L35	Refrigeration factor L35 L35 (EER) 50 Hz: 2.4 Refrigeration factor L35 L35 (EER) 60 Hz: 1.95
Version	roof-mounted
Dimensions	Width: 597 mm Height: 417 mm Depth: 475 mm
Protection category IP to EN 60 529	External circuit, IP 34 Internal circuit, IP 54
Refrigerant/cooling medium	Refrigerant: R-513A Quantity: 0.65 kg Global Warming Potential (GWP): 631 CO ₂ equivalent (CO ₂ e): 0.41 t
Type of connection (electrical)	Plug-in terminal strip
Duty cycle	100 %
Temperature control	e-Comfort Controller (factory setting +35 °C)
Operating temperature range	10 °C...55 °C
Operating temperature max @60 Hz	53 °C
Storage temperature range	-40 °C...70 °C

Features

Setting range	20 °C...53 °C
Rated power Pel	Rated power L35 L35/50 Hz: 0.42 kW Rated power L35 L35/60 Hz: 0.56 kW Rated power L35 L50/50 Hz: 0.48 kW Rated power L35 L50/60 Hz: 0.65 kW
Permissible operating pressure (p. max.)	28 bar
Pre-fuse	Transformer circuit-breaker: 6.3...10 A
Packaging unit	1 pc(s).
Net weight	46.55 kg
Gross weight	49 kg
Customs tariff number	84158200
ETIM 9	EC000855
ETIM 8	EC000855
ECLASS 8.0	27180704
Product description	SK cooling unit Blue e, roof-mounted, 3412 BTU/h, 400 V, 2~, 50/60 Hz, carbon steel, WHD: 597 x 417 x 475 mm

Approvals

Approvals	UL + C-UL (listed) UL + C-UL - FTTA
Explanations	Declaration of conformity Declaration of conformity - F-gas regulation Declaration of conformity UK