### Rittal – The System.

Faster – better – everywhere.





# SV 3433.040 Bus-Mounting Fuse Element

State: 2025-10-16 (Source: rittal.com/ca-en)



## SV 3433.040 - Bus-Mounting Fuse Element

3-pole, for 60 mm bar center distance.

#### **Features**

Model No.	SV 3433.040
Version	Easy Connect
Material	Bus-mounting fuse base: Fiberglass-reinforced, thermoplastic polyester (PBT) Contact hazard protection: Polyamide Fire protection corresponding to UL 94-V0 Contact hazard protection: Polyamide
Color	RAL 7035
Supply includes	Pre-assembled component ready for connection including contact hazard protection and exterior terminals.
Note	Wire end ferrules should be used with fine stranded wire conductors
For bar systems with center-to- center spacing	60 mm
Type of connection (electrical)	Box terminal
Fuse inserts	D III-E 33 (adaptor screw)
Rated insulation voltage	690 V
Rated current max.	63 A
Rated operating voltage	690 V (DC) 690 V, 3~
Note	For the use of fuse inserts to DIN EN 60 269-3 (DIN VDE 0636-3)
Dimensions	Width: 71 mm Height: 251 mm
Connection of round conductors	1.5 - 16 mm²
Suitable for busbars	Height: 5, 10 mm
Number of poles	3-pole

© Rittal 2025

#### **Features**

Rated operating voltage (L1 + L2)	690 V (DC)
Rated operating voltage (L1 + L3)	690 V (DC)
Packaging unit	5 pc(s).
Net weight	2
Gross weight	2.496
Copper weight (kg per piece)	0.119
Customs tariff number	85369095
EAN	4028177675018
ETIM 9	EC001644
ETIM 8	EC001644
ECLASS 8.0	27142120

# **Approvals**

Approvala	ADC
Approvals	ABS DNV-GL
	Lloyds Register of Shipping
Explanations	Declaration of conformity

© Rittal 2025 3