


# Rittal – The System.

Faster – better – everywhere.



## SV 3451.500 Conductor terminal

State: 2025-08-13 (Source: [rittal.com/ca-en](https://rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 3451.500 - Conductor terminal

For connecting round conductors and laminated copper bars.

## Features

|   |  |
|---|--|
| Model No.                                       | SV 3451.500  |
| Product description                             | For connecting round conductors and laminated copper bars.   |
| Material  | Carbon steel   |
| Surface finish                                  | Zinc-plated, passivated  |
| Clamping area for laminated copper bars (W x H) | 8 x 8 mm   |
| Note  | Wire end ferrules should be used with fine stranded wire conductors  |
| Connection of round conductors                  | 2.5 - 16 mm <sup>2</sup>   |
| For busbar thickness                            | 5 mm   |
| Packaging unit                                  | 15 pc(s).  |
| Net weight                                      | 0.375  |
| Gross weight                                    | 0.44   |
| PCF/VE (cradle-to-gate)                         | 1.6 kg CO2 eq (Cat B)  |
| Information regarding the PCF class             | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number                           | 85369010   |
| EAN   | 4028177042681  |
| ETIM 9  | EC000001   |
| ETIM 8  | EC000001   |
| ECLASS 8.0                                      | 27141146   |

# Approvals

|              |   |
|--------------|---|
| Approvals    | UR + C-UR (recognized)                                    |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |