


**Rittal – The System.**

Faster – better – everywhere.



**SV 3433.010**

**Bus-Mounting Fuse Element**

State: 2026-02-14 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# SV 3433.010 - Bus-Mounting Fuse Element

3-pole, for 60 mm bar center distance.

## Features

Model No.	SV 3433.010
Material	Bus-mounting fuse base: Fiberglass-reinforced, thermoplastic polyester (PBT) Contact hazard protection: Polyamide Fire protection corresponding to UL 94-V0
Color	RAL 7035
Note	Wire end ferrules should be used with fine stranded wire conductors
For bar systems with center-to-center spacing	60 mm
Type of connection (electrical)	Box terminal
Fuse inserts	D III-E 33 (adaptor screw)
Rated insulation voltage Ui	690 V
Rated current max.	63 A
Rated operating voltage	690 V (DC) 690 V, 3~
Note	For the use of fuse inserts to DIN EN 60 269-3 (DIN VDE 0636-3)
Dimensions	Width: 57 mm Height: 209 mm
Connection of round conductors	1.5 - 25 mm <sup>2</sup>
Suitable for busbars	Height: 5, 10 mm
Number of poles	3-pole
Rated operating voltage (L1 + L2)	690 V (DC)
Rated operating voltage (L1 + L3)	690 V (DC)
Round conductor cross-section	1.5 - 25 mm <sup>2</sup>

# Features

---

Packaging unit	10 pc(s).
Net weight	3
Gross weight	3.18
Copper weight (kg per piece)	0.071
Customs tariff number	85369095
EAN	4028177674998
ETIM 9	EC001644
ETIM 8	EC001644
ECLASS 8.0	27142120

---

# Approvals

---

Approvals	ABS DNV-GL Lloyds Register of Shipping
Explanations	Declaration of conformity

---