


Rittal – The System.

Faster – better – everywhere.



SV 3458.500 Conductor terminal

State: 2025-12-19 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 3458.500 - Conductor terminal

For connecting round conductors and laminated copper bars.

Features

| | |
|---|--|
| Model No. | SV 3458.500 |
| Product description | For connecting round conductors and laminated copper bars. |
| Material | Carbon steel |
| Surface finish | Zinc-plated, passivated |
| Clamping area for laminated copper bars (W x H) | 16.5 x 15 mm |
| Note | Wire end ferrules should be used with fine stranded wire conductors |
| Connection of round conductors | 35 - 70 mm ² |
| For busbar thickness | 10 mm |
| Packaging unit | 15 pc(s). |
| Net weight | 1.65 |
| Gross weight | 1.679 |
| PCF/VE (cradle-to-gate) | 6.3 kg CO2 eq (Cat B) |
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number | 85369010 |
| EAN | 4028177042766 |
| ETIM 9 | EC000001 |
| ETIM 8 | EC000001 |
| ECLASS 8.0 | 27141146 |

Approvals

| | |
|--------------|---|
| Approvals | UR + C-UR (recognized) |
| Explanations | Declaration of conformity Declaration of conformity UK |