

Rittal – The System.

Faster – better – everywhere.



SV 3439.010

Connection Adapters

State: 2026-02-01 (Source: [ittal.com/ca-en](https://www.ittal.com/ca-en))



FRIEDHELM LOH GROUP

SV 3439.010 - Connection Adapters

For busbar systems with 60 mm center-to-center distance.

Features

Model No.	SV 3439.010
Material	Cover: ABS Chassis: Fiberglass-reinforced, thermoplastic polyester (PBT) Fire protection corresponding to UL 94-V0
Color	RAL 7035
Rated current max.	600 A
Rated operating voltage	690 V, 3~
Cable outlet	Top/bottom
For bar systems with center-to-center spacing	60 mm
Note	The technical data may vary for UL applications. UL approval only applies in conjunction with AC application The rated operating voltage for DC applications depends on the busbar arrangement in the busbar support 9340.050/9341.050/9342.050.
Number of poles	3-pole
Dimensions	Width: 180 mm Height: 247 mm
Connection of round conductors, multi-wire	35 - 240 mm ²
Suitable for busbars	Height: 5, 10 mm
Clamping area for laminated copper bars (W x H)	24 x 21 mm
Packaging unit	1 pc(s).
Net weight	4.36
Gross weight	4.635

Features

Copper weight (kg per piece) 0.732

Customs tariff number 85369010

EAN 4028177236295

ETIM 9 EC001531

ETIM 8 EC001531

ECLASS 8.0 27370304

Approvals

Approvals ABS

Explanations Declaration of conformity
Declaration of conformity UK