

Rittal – The System.

Faster – better – everywhere.



SV 3568.005 Laminated Copper Bar

State: 2026-04-04 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 3568.005 - Laminated Copper Bar

Cu lamina made of high-purity electrolyte copper, length: 2000 mm/bar.



Features

| | |
|---|---|
| Model No. | SV 3568.005 |
| Material | Cu lamina: High-purity electrolyte copper Insulation: Highly resistant vinyl blend, expansion 370%, temperature: -30°C ... +105°C, fire protection according to UL-94 V0, dielectric strength: 20 kV/mm |
| Length | 2,000 mm |
| Rated current for temperature increase 50 K | 350 A |
| Rated current for temperature increase 30 K | 265 A |
| Rated current for temperature increase 70 K | 415 A |
| Note | Assembly = number of layers x layer width x layer thickness May be cut to length as required The conductor temperature of the laminated copper bar is derived by adding the ambient temperature and the temperature increase together. Example: 3565.005 carrying 180 A, i.e. the temperature increases by 30 K. At an ambient temperature of 35 °C, this produces a resultant conductor temperature of 35 °C + 30 K = 65 °C. |

Features

| | |
|-------------------------------|--|
| Laminated flat copper version | Number of lamina: 6 Lamina width: 15.5 mm Lamina thickness: 0.8 mm |
| Packaging unit | 1 pc(s). |
| Net weight | 1.616 kg |
| Gross weight | 1.816 kg |
| Copper weight (kg per piece) | 1.33 |
| Customs tariff number | 85446010 |
| ETIM 9 | EC001522 |
| ETIM 8 | EC001522 |
| ECLASS 8.0 | 27370303 |
| Product description | SV Laminated copper bar, WH: 15,5x4,8 mm, L: 2000 mm |

Approvals

| | |
|--------------|---|
| Approvals | UR + C-UR (recognized) |
| Explanations | Declaration of conformity Declaration of conformity UK |