

Rittal – The System.

Faster – better – everywhere.



SV 3577.005 Laminated Copper Bar

State: 2025-11-17 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 3577.005 - Laminated Copper Bar

Cu lamina made of high-purity electrolyte copper, length: 2000 mm/bar.



Features

Model No.	SV 3577.005
Material	Cu lamina: High-purity electrolyte copper Insulation: Highly resistant vinyl blend, expansion 370%, temperature: -30°C ... +105°C, fire protection according to UL-94 V0, dielectric strength: 20 kV/mm
Length	2,000 mm
Rated current for temperature increase 50 K	940 A
Rated current for temperature increase 30 K	710 A
Rated current for temperature increase 70 K	1,125 A
Note	Assembly = number of layers x layer width x layer thickness May be cut to length as required The conductor temperature of the laminated copper bar is derived by adding the ambient temperature and the temperature increase together. Example: 3565.005 carrying 180 A, i.e. the temperature increases by 30 K. At an ambient temperature of 35 °C, this produces a resultant conductor temperature of 35 °C + 30 K = 65 °C.

Features

Laminated flat copper version	Number of lamina: 5 Lamina width: 50 mm Lamina thickness: 1 mm
Packaging unit	1 pc(s).
Net weight	9.841
Gross weight	10.359
Copper weight (kg per piece)	4.48
Customs tariff number	74071000
EAN	4028177666832
ETIM 9	EC001522
ETIM 8	EC001522
ECLASS 8.0	27370303

Approvals

Approvals	UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity UK