
Rittal – The System.

Faster – better – everywhere.






SV 3584.020 Busbars CUPONAL

State: 2025-12-01 (Source: rittal.com/ca-en)



SV 3584.020 - Busbars CUPONAL

Copper-coated aluminum busbars.



Features

| Model No. | SV 3584.020 |
|------------------------------|--|
| Product description | Copper-coated aluminum busbars, suitable for configuring busbar systems with busbar supports SV 9340.000/SV 9340.050. |
| Material | Aluminum Copper |
| Length | 2,400 mm |
| Rated current max. | 328 A |
| Note | The rated current is generated at 65°C rail temperature and 35°C ambient temperature Correction factor diagram according to DIN EN 43 671 May be cut to length as required |
| Standards | DIN EN 13 601 |
| Cross-section | 30 mm x 5 mm |
| Dimensions | Length: 2,400 mm |
| Packaging unit | 6 pc(s). |
| Net weight | 8.52 |
| Gross weight | 9 |
| Copper weight (kg per piece) | 0.52 |

© Rittal 2025

Features

| Customs tariff number | 74071000 |
|-----------------------|---------------|
| EAN | 4028177686571 |
| ETIM 9 | EC001522 |
| ETIM 8 | EC001522 |
| ECLASS 8.0 | 27370303 |

Approvals

| Explanations | Declaration of conformity |
|--------------|------------------------------|
| | Declaration of conformity UK |

© Rittal 2025 3