

Rittal – The System.

Faster – better – everywhere.



SV 3582.020 Busbars CUPONAL

State: 2025-08-10 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 3582.020 - Busbars CUPONAL

Copper-coated aluminum busbars.



Features

Model No.	SV 3582.020
Product description	Copper-coated aluminum busbars, suitable for configuring busbar systems with busbar supports SV 9340.000/SV 9340.050.
Material	Aluminum Copper
Length	2,400 mm
Rated current max.	235 A
Note	The rated current is generated at 65°C rail temperature and 35°C ambient temperature Correction factor diagram according to DIN EN 43 671 May be cut to length as required
Standards	DIN EN 13 601
Cross-section	20 mm x 5 mm
Dimensions	Length: 2,400 mm
Packaging unit	6 pc(s).
Net weight	4.5
Gross weight	6.42
Copper weight (kg per piece)	0.35

Features

Customs tariff number	74071000
EAN	4028177686557
ETIM 9	EC001522
ETIM 8	EC001522
ECLASS 8.0	27370303

Approvals

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---