

Rittal – The System.

Faster – better – everywhere.



HD 4000.062 Command panel HD

State: 2026-05-14 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



HD 4000.062 - Command panel HD

Monitors, PC and other components with displays are hygienically and securely protected in the command panel. The roof slope of 30° prevents objects from being collected on top and allows liquid to run off quickly.

Features

Model No.	HD 4000.062
Benefits	Roof slope 30° towards the front Height-adjustable mounting board for screens up to 24" in size Bracket for TFT table height adjustable for screens up to 24"
Material	Housing and door: Stainless steel 1.4301 (AISI 304) HD lock inserts: Stainless steel 1.4404 (AISI 316L) Viewing window: Polycarbonate Seal: Silicone, compliant with FDA Guideline 21 CFR 177.2600 Viewing window: Polycarbonate
Surface finish	Housing and door: Brushed, grain 400, peak-to-valley height < 0.8 µm Seal: Blue, dyed (RAL 5010)
Supply includes	Housing of all-round solid construction Door with viewing window and inserted seal R/h door catch Holder for desktop TFT with VESA 75/100 locator
Options	without viewing window Mounting plate instead of mounting board Cut-out for touch panel instead of viewing panel Keyboard Support HD
Dimensions	Width: 810 mm Height, front: 692 mm Height rear: 848 mm Depth: 266 mm
Visible area	Viewing window width: 535 mm Viewing window height: 325 mm
Material thickness - enclosure	1.5 mm

Features

Material thickness - door	2 mm
Protection category NEMA	NEMA 4X
IK code	IK08
Packaging unit	1 pc(s).
Net weight	33.2 kg
Gross weight	33.2 kg
Customs tariff number	94032080
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

Approvals

Explanations	PCF-declaration
--------------	-----------------