

Rittal – The System.

Faster – better – everywhere.



AS 4050.200 Assembly frame

State: 2026-06-24 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.200 - Assembly frame

The assembly frames are mobile, tiltable and (depending on the version) height-adjustable frames for the mounting of plates and enclosures.

Features

Model No.	AS 4050.200
Version	200 EN (electrically tilt-adjustable)
Product description	The assembly frames are mobile, tiltable and (depending on the version) height-adjustable frames for the mounting of plates and enclosures.
Benefits	Allows ergonomic and back-friendly working Individually positionable in the workshop, as it is independent from the power network Minimal space required when not in use Easy handling thanks to four casters including complete locking function Variable fixing of mounting plates using quick-release fasteners
Technical specifications	Incline can be adjusted from approximately 0 – 80°
Supply includes	Assembly frame 1 VE clamping unit at bottom 1 packing unit with top clamping unit Charger Rechargeable battery
Note	With the assembly frame extension, a maximum machining area of 1900 x 1900 mm can be achieved.
Machine dimensions	Width: 1,400 mm Depth: 1,250 mm
Dimensions support surface max.	Width: 1,110 mm Height: 1,900 mm
Dimensions support surface min.	Width: 1,110 mm Height: 1,230 mm
Load	200 kg

Features

Working height	Working height (min.): 90 cm Working height (max.): 90 cm
Packaging unit	1 pc(s).
Net weight	130 kg
Gross weight	148 kg
Customs tariff number	84279000
ETIM 9	EC002224
ETIM 8	EC002224
ECLASS 8.0	36659090
Product description	Assembly frame 200 EN

Approvals

Explanations	Declaration of conformity
--------------	---------------------------