

Rittal – The System.

Faster – better – everywhere.



AS 4050.318 Thread cutting option

State: 2025-08-19 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.318 - Thread cutting option for Perforex LC 3030

Thread cutting option for Perforex LC laser center including thread tap with clamping units for M3 – M10.



Features

Model No.	AS 4050.318
Version	Moveable tool magazine with 6 magazine slots Tool holder Additional drive unit
Product description	Thread tapping option for the Perforex LC laser center.
Benefits	Machining of projects with tapped holes possible Fast, automatic changeover from laser function to thread cutting function by accommodating an additional machining head
Supply includes	Thread tap Including clamping units for M3 – M10
Machinable height (max.)	600 mm
Material thickness:	5 mm
Suitable for Model No.	4050330
Packaging unit	1 pc(s).
Net weight	78
Gross weight	78
Customs tariff number	84669360
EAN	4028177806658
ECLASS 8.0	36600890