

Rittal – The System.

Faster – better – everywhere.



AS 4050.450 Cutting machine C8

State: 2025-07-18 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.450 - Cutting machine C8

Semi-automatic machine for cutting wires to custom dimensions.

Features

Model No.	AS 4050.450
Version	With control panel
Product description	Semi-automatic machine for cutting wires to customized dimensions.
Benefits	Easy operation Easy insertion of wires Simple opening of feed rollers PC compatible
Technical specifications	Individual conductor, fine-wire, 0.08 - 10 mm ² (AWG 28 - 8) Individual conductor, single-wire, 0.08 - 2.5 mm ² (AWG 28 - 14) For wire lengths 1 - 99999 mm Feed rate 0 - 1.5 m/s Controllable pressing force of feed rollers Servo DC drive
Supply includes	Cutting machine C8 Software on CD-ROM Connection cable with connector
Rated operating voltage	100 V - 240 V, 1~, 50 Hz/60 Hz
Apparent power	120 VA
Machine dimensions	Width: 380 mm Height: 470 mm Depth: 360 mm
Packaging unit	1 pc(s).
Net weight	24
Gross weight	24
Customs tariff number	84798997
EAN	4028177804845

Features

ECLASS 8.0

36600890