


Rittal – The System.

Faster – better – everywhere.



AS 4050.452 Crimping Machine L8

State: 2025-08-06 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.452 - Crimping Machine L8

Electro-pneumatically driven wire stripping and crimping center that can process loose, insulated wire end ferrules.

Features

Model No.	AS 4050.452
Version	Touchscreen display
Product description	Electro-pneumatically driven wire stripping and crimping center that can process loose, insulated wire end ferrules.
Benefits	Easy operation Secure, fast processing of insulated wire end ferrules No set-up time thanks to automatic tool change Processing of special wires possible Simple, quick component mounting Automatic recognition of cross-sections
Technical specifications	Crimping range 0.5–2.5 mm ² (AWG 20 - 14) Crimping length 8 mm (0.31 in.) Insertion length 35 mm (1.378 in.) Wire end ferrules with a plastic collar can be produced in special sizes
Supply includes	Crimping Machine L8 1 swivel feeder bowl 0.5–1.5 mm ² 1 swivel feeder bowl 1.5–2.5 mm ²
Note	Standard crimping shape, trapezium - others available upon request
Dimensions	Width: 390 mm Height: 460 mm Depth: 330 mm
Compressed air connection	5.5 bar
Rated operating voltage	100 V - 240 V, 1~, 50 Hz/60 Hz
Apparent power	110 VA
Crimping	Trapezoid crimp
Cycle time	1.5 s

Features

Packaging unit	1 pc(s).
Net weight	34.6
Gross weight	34.67
Customs tariff number	84798997
EAN	4028177804869
ETIM 9	EC002778
ETIM 8	EC002778
ECLASS 8.0	36600890