

Rittal – The System.

Faster – better – everywhere.



AS 4050.454

Automatic Crimping Machine R8 E

State: 2026-02-12 (Source: rittal.com/ca-en)



FRIEDHELM LOH GROUP

AS 4050.454 - Automatic Crimping Machine R8 E

Electrically driven wire stripping and crimping center that can process reel-mounted, insulated wire end ferrules.



Features

Model No.	AS 4050.454
Version	Touchscreen display
Product description	Electrically driven wire stripping and crimping center that can process reel-mounted, insulated wire end ferrules.
Benefits	<ul style="list-style-type: none">Easy operationFast adjustmentFlexible use in the workshopFast replacement of consumables
Technical specifications	<ul style="list-style-type: none">Crimping range 0.5–2.5 mm² (AWG 20 - 14)Crimping length 8 mm (0.31 in.)Insertion length 40 mm (1.57 in.)
Note	Standard crimping shape, trapezium - others available upon request
Dimensions	<ul style="list-style-type: none">Width: 288 mmHeight: 230 mmDepth: 345 mm
Rated operating voltage	100 V - 240 V, 1~, 50 Hz/60 Hz
Apparent power	100 VA
Crimping	Trapezoid crimp
Cycle time	1.8 s
Packaging unit	1 pc(s).

Features

Net weight	16
Gross weight	16
Customs tariff number	84798997
EAN	4028177813465
ETIM 9	EC002778
ETIM 8	EC002778
ECLASS 8.0	36600890
