Rittal – The System.

Faster – better – everywhere.





AS 4050.454 Automatic Crimping Machine R8 E

State: 2025-11-08 (Source: rittal.com/ca-en)



AS 4050.454 - Automatic Crimping Machine R8 E

Electrically driven wire stripping and crimping center that can process reel-mounted, insulated wire end ferrules.





Features

Model No.	AS 4050.454
Version	Touchscreen display
Product description	Electrically driven wire stripping and crimping center that can process reel-mounted, insulated wire end ferrules.
Benefits	Easy operation
	Fast adjustment
	Flexible use in the workshop
	Fast replacement of consumables
Technical specifications	Crimping range 0.5–2.5 mm² (AWG 20 - 14)
	Crimping length 8 mm (0.31 in.)
	Insertion length 40 mm (1.57 in.)
Note	Standard crimping shape, trapezium - others available upon request
Dimensions	Width: 288 mm
	Height: 230 mm
	Depth: 345 mm
Rated operating voltage	100 V - 240 V, 1~, 50 Hz/60 Hz
Apparent power	100 VA
Crimping	Trapezoid crimp
Cycle time	1.8 s
Packaging unit	1 pc(s).

© Rittal 2025

Features

Net weight	16
Gross weight	16
Customs tariff number	84798997
EAN	4028177813465
ETIM 9	EC002778
ETIM 8	EC002778
ECLASS 8.0	36600890

© Rittal 2025 3