

Rittal – The System.

Faster – better – everywhere.



AS 4050.455

C8+ automatic cutting machine

State: 2025-08-02 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.455 - C8+ automatic cutting machine

Semi-automatic machine for cutting wires to customized dimensions.

Features

Model No.	AS 4050.455
Version	With control panel Stop & go function
Product description	Semi-automatic machine for cutting wires to customized dimensions.
Benefits	Easy to operate Easy insertion of wires Simple opening of feed rollers PC compatible Length-cutting with interface to CAE data supported Supports the cable marking process by displaying the connection points on the display Easy transferring of projects and orders to the C8+ cutting machine
Technical specifications	Individual conductor, fine-wire, 0.08 - 10 mm ² (AWG 28 - 8) Individual conductor, single-wire, 0.08 - 2.5 mm ² (AWG 28 - 14) For wire lengths 1 - 99999 mm Feed rate 0 - 1.5 m/s Controllable pressing force of feed rollers Servo DC drive Insertion length 27 mm (1.06 in.)
Supply includes	C8+ automatic cutting machine Connection cable with connector CAE data software connection Installation CD
Interfaces	EPLAN Pro Panel CAE data
Dimensions	Width: 380 mm Height: 470 mm Depth: 360 mm
Rated operating voltage	100 V - 240 V, 1~, 50 Hz

Features

Apparent power	240 VA
Cycle time	2 s
Packaging unit	1 pc(s).
Net weight	19.74
Gross weight	20.74
Customs tariff number	84798997
EAN	4028177930858
ETIM 9	EC002778
ETIM 8	EC002778
ECLASS 8.0	36629090