

# Rittal – The System.

Faster – better – everywhere.



## AS 4050.749 Wire end ferrule

State: 2026-06-25 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4050.749 - Wire end ferrule on belt

With plastic flange.

## Features

Model No.	AS 4050.749
Version	For assembly machines
Product description	With plastic flange.
Technical specifications	Heat resistant up to 105 °C
Material	E-Cu, tin-plated Plastic collar: Polypropylene
Color	Black
Suitable for	Enclosure type: Automatic crimping machine RC Automatic crimping machine R8 Automatic crimping machine R8 E
Length	8 mm
AWG	16
Internal diameter	3.5 mm
For cross section	1.5 mm <sup>2</sup>
DIN color code	Yes
Note	UL-certified in conjunction with the relevant tools, e.g. crimping machines.
Delivery form	Taped
Packaging unit	5,000 pc(s).
Net weight	5 kg
Gross weight	0.722 kg
Customs tariff number	85369010
ETIM 9	EC000005
ETIM 8	EC000005

# Features

---

ECLASS 8.0

36659290

---

Product description

Wire end ferrules According to DIN colour code

# Approvals

---

Approvals

UL + C-UL (listed)

UR